


AXOLUTE **Temperature control** and electronic control devices

Cat. No(s): HD4451 - HC4451 - HS4451 - HD4441 - HC4441 - HS4441 HD4442 - HC4442 - HS4442 - HD4431 - HC4431 - HS4431 - HD4432 - HC4432 - HS4432 HD4432V127 - HC4432V127 - HS4432V127




1. USE

Electronic and timer thermostats range and passive infrared switches.

2. RANGE

	Designation	References
	Electronic room thermostat Relay output with 1 switching contact 2 A - 250 Vac Power supply 230 Vac. 2 modules	□ HD4441 ■ HC4441 ■ HS4441
	Electronic room thermostat with a built-in «summer/ winter» changeover switch - Relay output with a C-NO 2 A 250 Vac contact - Power supply 230 Vac. 2 modules	□ HD4442 ■ HC4442 ■ HS4442
	Daily/weekly electronic chronothermostat for heating ad conditioning systems - Backlighted display Power supply with battery 2 x 1.5 V Control possibility by a remote teleactivation and connection with an external temperature probe Output contact in exchange 5 A - 3 modules	□ HD4451 ■ HC4451 ■ HS4451
	Switch with passive IR movement detector - Variable threshold wilight circuit with possibility to be exclused. Timing circuit for switch-off delay, adjustable from 30 seconds to 10 minutes. Relay output 2 A resistive/2 A inductive. Power supply 230 Vac - 1 module	□ HD4431 ■ HC4431 ■ HS4431
	Switch with passive IR movement detector - Variable threshold wilight circuit with possibility to be exclused. Timing circuit for switch-off delay, adjustable from 30 seconds to 10 minutes can also be activated with external pushbutton. Relay output 6 A resistive/2 A inductive. With selector 0-A-1 - Power supply 230 Vac. 2 modules	□ HD4432 ■ HC4432 ■ HS4432
	As above - 110 - 127 Vac.	□ HD4432V127 ■ HC4432V127 ■ HS4432V127
Index of colou Uhite Tech Anthracite Neutral	rs:	

3. OVERALL DIMENSIONS (mm)



	А	В	С	D
1 module	45	22.5	33.5	9.5
2 modules	45	45	33.5	9.5
3 modules	45	68	31.5	18.5

4. CONNECTION

Screw clamps:

Terminal capacity: 1.5 mm² / 2.5 mm² Stripping length (rigid or flexible cable): 9 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D Impact test: IK 04

5.2 Material characteristics

- Material:
- Polycarbonate for mechanism case - ABS for key cover
- Halogen free UV resistant.
- Self extinguishing:
 - 850° C / 30 s for insulating parts holding live parts in place.
- 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Climatic characteristics

Storage and operating temperatures: + 5° C to + 35° C

AXOLUTE

Temperature control and electronic control devices

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

Designation	Cat. No.
GSM telephone actuator - 4 DIN modules	○ F462
External probe for N/NT/L4450 and N/NT/L4451	○ 3457

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e.catalogue.