

Cat. No(s): H4702G - H4702 - H4703 - H4704 - H4706 - H4726

# **Supporting frames**



H4704

## 1. USE


Supporting frames for mounting Axolute mechanisms.

The supporting frames are supplied with a pre-installed orange frame-cover and a transparent protection.

## 2. RANGE

Supports for flush-mounting Ita	orts for flush-mounting Italian boxes (masonry and dry partition) Fixing centre		References
	Support with screws - 2 modules For square and elliptic cover plates	60 mm	H4702
	Support with claws - 2 modules For square and elliptic cover plates	60 mm	H4702G
	Support with screws - 3 modules For rectangular and elliptic cover plates	83.5 mm	H4703
	Support with screws - 4 modules PFor rectangular and elliptic cover plates	108.5 mm	H4704
	Support with screws - 6 modules For rectangular and elliptic cover plates	100 x 60 mm	H4706
	Support with screws - 3 + 3 modules For rectangular and elliptic cover plates	46 x 83.5 mm	H4726

## 3. OVERALL DIMENSIONS (mm)



Supports	Α	В	С
H4702	75.2	75.2	60
H4702IT	75.2	75.2	60
H4703	73	115	83.5
H4704	73	137	108.5
H4706	73	184.2	100 x 60
H4726	118	112	46 x 83.5

Technical data sheet: F01803EN/00 Updated: Created: 14/05/2013



## **Supporting frames**

## 4. MOUNTING

The supporting frames are screwed to flush mounting boxes. Claw-fitted for the reference H4702G.

## **5. TECHNICAL CHARACTERISTICS**

#### ■ 5.1 Material characteristics

Supports are in stainless steel and polycarbonate glass fiber filled. For the reference H4702G: the support is made of stainless steel and

#### ■ 5.2 Electrical characteristics

Self-extinguishing: 650° C / 30 s

## ■ 5.3 Climatic characteristics

Storage temperature: -  $10^{\circ}$  C to +  $70^{\circ}$  C Use temperature: - 5° C to + 50° C

Created: 14/05/2013