


Valena™ Double USB socket - Type-A - 3.0 A

Cat. No(s): 7 702 70 - 7 704 70 - 7 741 70




1. USE

For recharging portable devices such as phones, smartphones, tablets, MP3 or MP4 players, loudspeakers, watches, game consoles, powerbanks.

2. RANGE

Description	Aluminium	White	Ivory
Double USB sockets - 5 V $\overline{\text{=}}$ - 3.0 A Mechanisms equipped with cover plate, support frame and claws. To be equipped with plates.	7 702 70	7 704 70	7 741 70

3. DIMENSIONS (mm)



A	B	C	D
71	71	42	12.5

4. CONNECTION

Type of terminals: with screws
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 6 mm
 Screwdriver: flat 3.5 mm
 Circuit breaker: 16 A MAXI

Necessary safety precautions:



**Switch OFF the power at the main circuit breaker.
 Make sure that the power is OFF before continuing with the installation.**

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04
 Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Base: PC V-0 class
 Cover-plate: PC / PC + ABS
 Cat. No 7 702 70: painted Aluminium
 Support frame: steel with surface treatment

Self-extinguishing:
 850°C/30 s for insulating components holding live parts in place.
 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	220 - 240 V~
Nominal input frequency	50-60 Hz
Maximum input current	300 mA
Maximum power consumption in standby	0.1 W
Power average efficiency	81 %
Nominal output voltage	5 V $\overline{\text{=}}$
Maximum output current	2400 mA
No-load power consumption class and average efficiency level: level VI*	
Safety-standard	EN60950-1
Protection class	II - Low voltage

*NB: European Regulation No. 278/2009 of 6 April 2009, Directive 2009/125/CE on eco-design requirements for AC/DC power supplies.

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

■ 5.4 Climate characteristics

Storage temperature: - 20°C to + 70°C
 Operating temperature: 0°C to + 40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.