


Mémoire Style Roller blind control 3 positions

Cat. No(s): AR-67121 - AR-67221



1. USE

3 switch positions «Up/Stop/Down» for direct drive motor.

2. RANGE

Description

AR-67121	● Steel brushed	Control roller blind 3 positions
AR-67221	● Gold brushed	

Note: Others finishes and configurations are provided, see technical data sheet F02217EN/01.

5. ASSEMBLY

- Do not use an electric screwdriver to tighten the screws when assembling wiring accessories.
- Take care not to overtighten the visible screws when assembling Mémoire style wiring accessories:
 - Risk of damaging the screw heads.
 - Risk of the screwdriver slipping and permanently scratching the plate.
 - Risk of the plate warping (bending), resulting in the plate not lying flat against the wall.
- Use a flat screwdriver (4 mm wide, 0.8 mm thick) for the screws supplied on the wiring accessory.
- ART d'Arnould electrical wiring accessories are supplied with long fixing screws which can be cut at several points to adapt the screw length to the box flush-mounting depth in the wall.


If ART d'Arnould wiring accessories are being mounted in thick surfaces such as tiles, marble, wainscot panelling with flush-mounting boxes chased deep into the wall, the whole screw length can be used to fix the wiring accessory.

If ART d'Arnould wiring accessories are being installed in walls with non-projecting flush-mounting boxes (masonry walls, dry partitions), the screws which can be cut at several points to shorten the thread.

To protect the products, it is essential to install them: once all surface coatings are completely dry, in a dry, non-aggressive environment, indoors only.

It is recommended that you install the plates only after the wall coatings have been completely finished (paint, fabrics, etc.).

4. DIMENSIONS (mm)



A	B	C	D
80	80	39.5	18.5

5. CONNECTION

Terminal type: with screws
 Capacity: 2 x 2.5 mm²
 Stripping length: 11 mm
 Compatible flexible or rigid cables
 Screwdriver: flat 4 mm

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Impact test: IK 02
 Ingress of solids/liquids: IP 20

■ 6.2 Material characteristics

Plate: Stainless steel + varnish

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place
 650°C/30 s for other insulating components

■ 6.3 Electrical characteristics

Voltage: 250 V~

Current: 6 AX

Frequency: 50/60 Hz

■ 6.4 Climate characteristics

Storage temperature: -10°C to +70°C

Operating temperature: -5°C to +35°C

7. CARE

Clean and dust using a soft, damp cloth (dampened with water) or wipes impregnated with a product containing less than 5% alcohol and anionic surfactant.

Caution: Always test before using other special cleaning products.

Banned products

- Solvents, various essential oils, paint, or adhesive tape,
- Scouring powders (because are abrasive),
- Products containing bleach,
- Special products for stainless steel,
- Renovators (because they often contain abrasives and chemical agents),
- Splashes or fumes from floor, paint, or wood stripping products, etc.

Caution:

Any mechanical attack or foreign object (screwdriver, etc.) striking the surface of the plate would damage the finish and therefore also the surface treatment.

8. STANDARDS AND APPROVALS

NF certified.

Compliant with installation and manufacturing standards.
See e.catalogue