



0 893 04



0 895 94



0 893 06L

1. DESCRIPTION

The use of DCL (lighting appliance) boxes and covers has been made compulsory.

For strip equipped with 2 P+E - 6 A automatic terminals.

Reinforced bezel, flush cover.

Cover guided into the box.

Can take IP 44 weatherproof cover (Cat. No. 0 895 04) for installation in damp areas (Vol II).


Supplied with blanking plate for protection while work is ongoing.

2. RANGE


DCL light boxes and covers		Cat. Nos.
	DCL strip box Ø 54 mm Depth 40 mm	0 893 04
	DCL strip box Ø 54 mm Depth 50 mm	0 893 05
	IP 44 cover for strip Ø 75 mm For mounting on boxes for wall lighting strips Cat. Nos. 0 893 04/05 and 0 892 04	0 895 04
	DCL cover for strip box Ø 67 mm For mounting on round Batibox boxes Cat. Nos. 0 804 51/61 to create a large-capacity wall lighting strip Ø 85 mm	0 895 94
	Strip box without DCL Ø 40 mm Depth 40 mm Supplied with cover	0 893 46
	Strip box Eco Batibox Airtight Depth 40 mm	0 893 06L

3. DIMENSIONS (mm)

Cat. Nos. 0 893 04/05/06L



Cat. No. 0 893 46



Cat. Nos.	Ø A	Ø B	C
0 893 04	54	59	40
0 893 05	54	59	50
0 893 06L	54	59	40
0 895 04	75	-	-
0 895 94	85	-	-
0 893 46	40	39	40

Cat. Nos.	Number of entries	
	16 mm	20 mm
0 893 04/05/06L	1	1
0 893 46	1	1

4. CONNECTION

Terminal type: automatic, oriented at 45°

Stripping length: 9 mm

2 entries for wires 1.5 mm²

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies/liquids: IP 20

IP 40 for Cat. No. 0 893 06L

IP 44 for Cat. No. 0 895 04

■ 5.2 Material characteristics

Casing: Polypropylene

Cover: Polypropylene

Screws: zinc-plated steel

UV resistance

Halogen-free

Self-extinguishing:

850°C/30 s for insulating parts holding live parts in place

650°C/30 s for other parts made of insulating materials

For Cat. No. 0 893 06L :

Casing: Polypropylene

Cover: Polypropylene

Screws: zinc-plated steel

End Caps: SEBS

UV resistance

With halogen

Self-extinguishing:

850°C/30 s for insulating parts holding live parts in place

■ 5.3 Electrical characteristics

Voltage: 250 V~

Current: 6 A

■ 5.4 Climate characteristics

Storage temperatures: -5°C to + 60°C

Operating temperatures: -5°C to +45°C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards

See legrand.com/ecatalogue