


Batibox[™] DCL centre point light box for masonry

Cat. No(s): 0 892 37



1. USE

The use of DCL (lighting appliance) boxes and covers has been made compulsory (see section 7 standards).

At the centre point, can be used to suspend up to 25 kg with rear attachment to framework, centre point is secured more quickly by using the anchoring device.


Boxes supplied with pipe hook and protective plate to prevent paint splashes.

Equipped with 4 entries Ø 16-20 mm.

2. RANGE

DCL centre point box	Cat. No.
DCL centre point box Ø 65 mm Depth 50 mm Equipped with an extra-slim protective cover (Cat. No. 0 895 90)	0 892 37

3. DIMENSIONS (mm)



Cat. No.	ØΑ	ØВ	С
0 892 37	80	65	65.5

4. CONNECTION

Terminal type: automatic, oriented at 45° Stripping length: 9 mm 2 entries for wires 1.5 mm²

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies/liquids: IP 20

■ 5.2 Materials characteristics

Casing: Red polypropylene Cover: White polypropylene

Hook: grey steel

Shaft: Fibreglass reinforced (25%) polyamide

UV-resistance Halogen-free

Self-extinguishing:

 850° C/30 s for insulating components holding live parts in place 650° C/30 s for other insulating components

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 6 A

■ 5.4 Climate characteristics

Storage temperatures: -5° C to $+60^{\circ}$ C Operating temperature: -5° C to $+40^{\circ}$ C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards See e-catalogue.