


Batibox[™] DCL strip light box for masonry

Cat. No(s): 0 892 04



1. USE

Luminaire box fitted with a DCL cover.

For strip equipped with 2 P+E - 6 A automatic terminals.

Reinforced bezel, flush cover.

Cover guided into the box.


Can take IP 44 weatherproof cover (Cat. No. 0 895 04) for installation in damp areas (Vol II).

Supplied with blanking plate for protection while work is ongoing.

2. RANGE

DCL strip box	Cat. No.
DCL strip box Ø 54 mm Depth 40 mm	0 892 04

3. DIMENSIONS (mm)



Cat. No.	Ø A	ØВ	С
0 892 04	60	54	40

Number of entries			
16 mm	20 mm		
1	1		

4. CONNECTION

Terminal type: automatic, oriented at 45° Stripping length: 9 mm 2 entries for wires 1.5 mm²

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies/liquids: IP 20

IP 44 with Cat. No. 0 895 04

■ 5.2 Materials characteristiques

Casing: Red polystyrene Cover: White polypropylene Screws : zinc-plated steel

UV-resistance
Halogen-free
Self-extinguishing:

 850° C/30 s for insulating components holding live parts in place 650° C/30 s for other insulating components

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 6 A

■ 5.4 Climate characteristics

Storage temperatures: -5°C to $+60^{\circ}\text{C}$ Operating temperature: -5°C to $+40^{\circ}\text{C}$

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

.....

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards See e-catalogue.