



Valena™ Life - Valena™ Allure
Rotary dimmer 300 W RLC + LEDs

Cat. No(s): 7 524 60 - 7 525 60 - 7 526 60
7 527 60 - 7 528 60 - 7 529 60/80



7 524 60
Valena Life



7 527 60
Valena Allure


1. USE

Rotary dimming for all types of lamps.
 Can be associated with one or several push buttons, for ON/OFF or dimming control.
 Integrates memory level function: the light switches ON the same level it has been switched OFF.
 Soft-start and soft-stop lighting (2 s).
 Mechanisms to be equipped with plates.
 Screw or claw mounting.

2. RANGE

Description	White	Ivory	Aluminium	Black
Rotary dimmer 300 W - 2-wires Supplied with support frame and rocker plate	7 524 60	7 525 60	7 526 60	-
	7 527 60	7 528 60	7 529 60	7 529 80

3. OVERALL DIMENSIONS (mm)




Cat. Nos	A	B	C	D
7 524 60 - 7 525 60 - 7 526 60	75	75	53.5	21.5
7 527 60 - 7 528 60 - 7 529 60/80	75	75	54.5	22

4. CONNECTION


4 terminals with screws
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 8 mm

5. INSTALLATION

Simple



With push buttons



6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 40
 Protection against impact: IK 02

■ 6.2 Material characteristics

Polygloss appearance
 Colour: - White RAL 9003
 - Ivory RAL 1013
 - Aluminium
 - Black

Material: - Front cover: ABS
 - Rocker: ABS
 - Halogen free
 - UV resistant

Material of the support: - Polycarbonate grey RAL 7037
 - Halogen free

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place
 + 650° C / 30 s for other parts made of insulating materials.















■ 6.3 Electrical characteristics

Voltage: 100 to 240 V~

Frequency: 50-60 Hz


Standby consumption: 0.2 W

● Load table

		R		L		C/L			
									
									
200 V / 240 V	Max.	300 W	300 W	300 VA	300 VA	300 VA	300 VA	75 W or 10 lamps max.	75 W or 10 lamps max.
	Min.	5 W	5 W	5 VA	5 VA	5 VA	5 VA	5 W	5 W
100 V / 200 V	Max.	150 W	150 W	150 VA	150 VA	150 VA	150 VA	37 W or 10 lamps max.	37 W or 10 lamps max.
	Min.	5 W	5 W	5 VA	5 VA	5 VA	5 VA	5 W	5 W

(*)Use only with transformers designed to function with electronic switches.

● Setting C or L



■ 6.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C

Use temperature: 0° C to + 35° C

7. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

8. STANDARDS AND APPROVALS

Compliance with standard IEC 60669-2-1

Compliance with standards of installation and manufacturing.

Refer to e. catalogue.