



Two-way switches and push button



6 639 01



6 639 02


1. USE

Lighting controls mechanisms.
 Complete products delivered.
 Flush-mounting or surface-mounting.
 Screw and/or claw fixing.
 Special renovation.

2. RANGE

Description	White
Two-way switch 10 AX	6 639 01
Double two-way switch 10 AX	6 639 02
Push button NO-NC 6 A	6 639 05

3. DIMENSIONS (mm)



A	B	C	D
86	86	42.5	14.5

4. CONNECTION

Type of terminals: automatic
 Terminals capacity: 2 x 2.5 mm²
 Stripping length: 13 mm
 Compatible flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20
 Protection against impact: IK 04

■ 5.2 Material characteristics

Polyglass appearance
 Colour: - White RAL 9003
 Material: - Mechanism housing: PC
 - Plate and rocker plate: ABS
 - Halogen free
 - UV resistant
 - Claws: steel

Material of the support: - PC grey RAL 7037 + 10 % glass fiber
 - Halogen free

Self-extinguishing:
 + 850° C / 30 s for insulating parts holding live parts in place
 + 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250 V~
 Current: - two-way switches: 10 AX
 - push button: 6 A
 Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C
 Use temperature: - 5° C to + 35° C

6. MAINTENANCE

Surface cleaning with a cloth.
 Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
 Refer to e. catalogue.