Synergy™
**Lighting control Push-buttons 10 A**
Authentic

Cat. No(s): 8 330 07 - 8 332 07 - 8 334 07


1. USE

Lighting controls push-buttons complete delivered, with compact mechanisms for maximum wiring space and slim front plates.
For flush-mounting, back box to be min. 35 mm deep.
Fixing with screws.

2. RANGE

Two-way push-button - 1-gang

8 330 07	⚪ Brushed stainless steel
8 332 07	⚪ Polished stainless steel
8 334 07	🟡 Glossy gold

3. OVERALL DIMENSIONS (mm)

Cat. Nos	A	B	C	D
8 33x 07	86	86	25	11

4. CONNECTION

Type of terminals : with screws
Terminal capacity: 4 x 1 mm² - 4 x 1.5 mm² - 2 x 2.5 mm² - 1 x 4 mm²
Stripping length: 8 mm
Compatible with flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics
Impact tests: IK 01
Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics
Rocker and plate:
- BSS: austenitic Brushed Stainless Steel - non magnetic - grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance
Mechanism housing: PC
Halogen free
UV resistant

Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place.
+ 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics
Voltage: 250 V~
Current: 10 A
Frequency: 50/60 Hz

■ 5.4 Climatic characteristics
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:
Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
See e.catalogue.