


Synergy™ Rotary dimmer 300 W RLC + LEDs Authentic

Cat. No(s): 8 331 51 - 8 333 51 - 8 335 51



1. USE

Rotary dimmer for all type of lamps.

Can be associated with one or several push-buttons, for ON/OFF or dimming control.

Integrates memory level function: when switched ON, gradually (2 s) lights up at the level set before last switch OFF.

Equipped with overvoltage and short-circuit protection.

Complete delivered, with compact mechanisms for maximum wiring space and slim front plates.


For flush-mounting, back box to be min. 35 mm deep. Fixing with screws.

2. RANGE

Push ON/OFF rotary universal dimmer - 1 gang

8 331 51	Brushed stainless steel
	Polished stainless stee
8 335 51	Glossy gold

3. OVERALL DIMENSIONS (mm)



Cat. Nos	Α	В	C	D
8 331 51 - 8 333 51 - 8 335 51	86	86	56	22

4. CONNECTION

Type of terminals: with screws Terminal capacity: 2 x 2.5 mm² Stripping length: 8 mm

Compatible with flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 01

Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Rocker and plate:

- BSS: austenitic Brushed Stainless Steel non magnetic grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance

Mechanism housing: PC

Knob: Zamak

Halogen free

UV resistant

Self-extinguishing:

- $+850^{\circ}$ C / 30 s for insulating parts holding live parts in place.
- + 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 100 to 240 V~

Frequency: 50/60 Hz

Stanby consumption: 0.2 W

For all types of lamps:

- dimmable LEDs: 5 W to 75W
- dimmable compact fluorescent lamps: 5 W to 75 W
- halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA
- fluorescent tube ballast: 5 VA to 300 VA
- halogen and incandescent 230 V: 5 W to 300 W

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.