

# **L<sup>1</sup> legrand**®

## Synergy™ Single pole socket outlets 13 A Authentic





Cat. No(s): 8 330 66/67/76/77 - 8 332 66/67/76/77 - 8 334 66/67/76/77


## 3. OVERALL DIMENSIONS (mm)

## 1. USE

Single pole socket outlets switched, complete delivered, with compact mechanisms for maximum wiring space and slim front plates. For flush-mounting, back box to be min. 35 mm deep. Fixing with screws.

## 2. RANGE

One-gang switched socket outlet with safety shutters					
8 330 66 8 332 66 8 334 66	<ul> <li>Brushed stainless steel</li> <li>Polished stainless steel</li> <li>Glossy gold</li> </ul>				
One-gang switched socket outlet + blue LED power indicator - with safety shutters					
8 330 67 8 332 67 8 334 67	<ul> <li>Brushed stainless steel</li> <li>Polished stainless steel</li> <li>Glossy gold</li> </ul>				
Two-gang switched socket outlet with safety shutters					
8 330 76 8 332 76 8 334 76	<ul> <li>Brushed stainless steel</li> <li>Polished stainless steel</li> <li>Glossy gold</li> </ul>				
Two-gang switched socket outlet + blue LED power indicator - with safety shutters					
8 330 77 8 332 77 8 334 77	<ul> <li>Brushed stainless steel</li> <li>Polished stainless steel</li> <li>Glossy gold</li> </ul>				



Cat. Nos	А	В	с	D
8 33x 66/67	86	86	31.5	10.5
8 33x 76/77	86	146	30	10.5

#### 4. CONNECTION

Type of terminals : with screws Terminal capacity: 3 x 2.5 mm<sup>2</sup> - 2 x 4 mm<sup>2</sup> - 2 x 6 mm<sup>2</sup> Stripping length: 12 mm Compatible with flexible or rigid cables.

#### **5. TECHNICAL CHARACTERISTICS**

#### 5.1 Mechanical characteristics

Impact tests: IK 01 Penetration by solid bodies/liquids: IP 20

Penetration by solid bodies/liquids: IP 2

## ■ 5.2 Material characteristics

- Rocker and plate:
- BSS: austenitic Brushed Stainless Steel non magnetic grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance Mechanism housing: PC

Halogen free

UV resistant

## Self-extinguishing:

- $+ 850^{\circ} \text{ C} / 30 \text{ s for insulating parts holding live parts in place.}$
- + 650° C / 30 s for other parts made of insulating materials.

## Synergy<sup>™</sup> Single pole socket outlets 13 A Authentic

### 5. TECHNICAL CHARACTERISTICS (continued)

#### 5.3 Electrical characteristics

Voltage: 250 V~ Current: 13 A Frequency: 50/60 Hz

## ■ 5.4 Climatic characteristics

Storage temperature: -  $10^\circ$  C to +  $70^\circ$  C Use temperature: -  $5^\circ$  C to +  $35^\circ$  C

## 6. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistance to the following cleaning substances:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

**Caution:** An initial test is required for the use of other special maintenance products.

## 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.