




Synergy™

Cat. No(s): 8 330 91/92/93/94 - 8 332 91/92/93/94 - 8 334 91/92/93/94

Front plates for Arteor mechanisms Authentic







1. USE

Front plates for Artor mechanisms. Flush-mounting or surface-mounting. Fixing with screws.

2. RANGE

8 330 94


8 332 94

8 334 94

1-gang for 1 Arteor module				
8 330 91 8 332 91 8 334 91	Brushed stainless steelPolished stainless steelGlossy gold			
1-gang for 2 Arteor modules				
8 330 92 8 332 92 8 334 92	Brushed stainless steel Polished stainless steel Glossy gold			
2-gang for 3 Arteor modules				
8 330 93 8 332 93 8 334 93	Brushed stainless steelPolished stainless steelGlossy gold			
2-gang for 4 Arteor modules				

3. OVERALL DIMENSIONS (mm)

Glossy gold



Brushed stainless steel

Polished stainless steel

3. OVERALL DIMENSIONS (mm) (continued)

Cat. Nos	Α	В	С	D
8 330 91 - 8 332 91 - 8 334 91 8 330 92 - 8 332 92 - 8 334 92	86	86	15	7.5
8 330 93 - 8 332 93 - 8 334 93 8 330 94 - 8 332 94 - 8 334 94	86	146	15	7.5

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 01

Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Plates:

- BSS: austenitic Brushed Stainless Steel non magnetic grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance

Support frame: PC

Halogen free

UV resistant

Self-extinguishing: 650° C / 30 s

■ 5.3 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

......

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.