




**Fused connection units double pole switched BS 13 A  
 Metalclad**



7 338 34



7 338 35



7 338 37


**1. USE**

British standard of fused connection units double pole switched, delivered complete for surface-mounting. Fixing with screws.

**2. RANGE**

Fused connection unit - Double pole switched - Without cord outlet	7 338 34
Fused connection unit - Double pole switched - With red LED power indicator	7 338 35
Fused connection unit - Double pole switched - With cord outlet	7 338 36
Fused connection unit - Double pole switched - With cord outlet + red LED power indicator	7 338 37

**3. OVERALL DIMENSIONS (mm)**



Cat. Nos	A	B	C	D
7 338 34/35/36/37	86	86	45	9

**4. CONNECTION**

Type of terminals: with screws  
 Terminal capacity (L+N+E)  
 Mains: 3 x 2.5 mm<sup>2</sup> - 2 x 2.5 mm<sup>2</sup> - 2 x 6 mm<sup>2</sup>  
 Load: 3 x 2.5 mm<sup>2</sup> - 2 x 4 mm<sup>2</sup> - 1 x 6 mm<sup>2</sup>  
 Stripping length: 12 mm  
 Compatible with flexible or rigid cables  
 7 338 36/37: Ø 12.5 mm flex outlet orifice in front plate  
 Cable clamp capable of restraining circular section cable to BS 6500 having 2 x 0.5 mm<sup>2</sup> section conductors.

**5. TECHNICAL CHARACTERISTICS**

■ **5.1 Mechanical characteristics**

Impact tests: IK 08  
 Penetration by solid bodies/liquids: IP 20

■ **5.2 Material characteristics**

Rocker: PC - Color: White and red  
 Front cover: PC - Color: White  
 Front plate and surface mounting back box: Grey epoxy coated steel  
 Mechanism housing: PP - Color: Grey  
 Halogen free  
 UV resistant

Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place.
- + 650° C / 30 s for other parts made of insulating materials.

■ **5.3 Electrical characteristics**

Voltage: 250 V~  
 Current: 13 A  
 Frequency: 50/60 Hz

■ **5.4 Climatic characteristics**

Storage temperature: - 10° C to + 70° C  
 Use temperature: - 5° C to + 35° C

**6. CLEANING**

Clean the surface with a cloth or soapy water.  
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

**Caution:** An initial test is required for the use of other special maintenance products.

**7. STANDARDS AND APPROVALS**

Compliance with standards of installation and manufacturing.  
 See e.catalogue.