



Synergy™ Blanking plate - Authentic

Cat. No(s): 8 330 95/96 - 8 332 95/96 - 8 334 95/96





1. USE

Blanking plates.

Flush-mounting or surface-mounting. Fixing with screws.

2. RANGE


One-gang blanking plates


8 330 95
8 332 95
9 Polished stainless steel
9 Polished stainless steel
Glossy gold

Two-gang blanking plates

8 330 96
8 332 96
Polished stainless steel
Polished stainless steel
Glossy gold

3. OVERALL DIMENSIONS (mm)





Cat. Nos	Α	В	С	D
8 33x 95	86	86	14	7
8 33x 96	86	146	14.5	7

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Impact tests: IK 01

Penetration by solid bodies/liquids: IP 20

■ 4.2 Material characteristics

- BSS: austenitic Brushed Stainless Steel non magnetic grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance

Halogen free

UV resistant

Self-extinguishing:

- +850° C / 30 s for insulating parts holding live parts in place.
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 4.3 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

5. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

6. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.