


Synergy™ Cable outlets - Authentic

Cat. No(s): 8 330 19/26 - 8 332 19/26 - 8 334 19/26



8 33x 19



8 33x 26

1. USE

Cable outlets, complete delivered, with slim front plates. For flush-mounting or surface-mounting. Fixing with screws.

2. RANGE


Cable outlets - 20 A


8 330 19	Brushed stainless steel
8 332 19	Polished stainless stee
8 334 19	Glossy gold

Cable outlets - 45 A

Brushed stainless steel Polished stainless steel
Glossy gold

3. OVERALL DIMENSIONS (mm)





Cat. Nos	Α	В	С	D
8 33x 19	86	86	34.5	22
8 33x 26	86	86	45	20

4. CONNECTION

Type of terminals: with screws Stripping length: 8 33x 19: 12 mm - 8 33x 26: 13 mm Compatible with flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 01

Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Plates:

- BSS: austenitic Brushed Stainless Steel non magnetic grade 304 L
- PSS: Polished Stainless Steel + rust resistance
- GG: Stainless Steel + rust resistance

Halogen free

UV resistant

Self-extinguishing:

- + 850° C / 30 s for insulating parts holding live parts in place.
- + 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.