


**Mosaic™**  
**Connected 2P+E socket - French standard**

Cat. No(s): 0 777 11LA




**1. USE**

Connected socket which can be controlled by a wireless lighting control and/or remotely via a smartphone, tablet or computer.  
 Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app.  
 Built-in protection against electrical overloads, for increased safety.  
 Installation in box 40 mm deep (minimum), instead of a standard socket outlet.  
 Claw and/or screw fixing.  
 One-piece mechanism (grid + mechanism).

**2. RANGE**

Description	White
Connected 2P+E socket, with safety shutter. With activity and identification LED indicator and RESET button (hidden) used to return to factory settings. Supplied with site protection cover. To be equipped with plate.	0 777 11LA

**3. DIMENSIONS (mm)**




A	B	C	D
74	74	41	10

**4. CONNECTION**


Terminal type: automatic  
 Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
 Stripping length: 11 mm

**5. OPERATION**



LED indicator:  
 - useful during installation  
 - indicator function can be activated in the Home + Control app

16 A connected socket outlet  
 Extra built-in protection in the event of overloads of more than 16 A



RESET button  
 used to return to factory settings

**6. TECHNICAL CHARACTERISTICS**

■ **6.1 Mechanical characteristics**

Protection against impacts: IK 04  
 Protection against solid bodies and/or liquids: IP 41 (mounted product)

■ **6.2 Material characteristics**

Rocker plate: PC  
 Colour: White RAL 9003  
 Mechanism casing: PC  
 Grid: 6.6 PC + Galfan steel

Halogen-free  
 UV-resistant

Self-extinguishing:  
 850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

## Connected 2P+E socket - French standard

### 6. TECHNICAL CHARACTERISTICS *(continued)*

#### ■ 6.3 Electrical characteristics

Voltage: 110/230 V~

Current: 16 A

Power: 3680 W max.

Frequency: 50/60 Hz

Standby consumption: 0.1 mA

**Zigbee technology** 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

Range: 200 m of unobstructed space between 2 wired products  
10 m between products indoors

#### ■ 6.4 Climate characteristics

Storage temperature: 0°C to +45°C

Usage temperature: +5°C to +45°C

### 7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

### 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 777 11LA) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: [www.legrandoc.com](http://www.legrandoc.com)