


ArteorTM Cat. Nos: 5 742 06/15/24/33

Connected Home/Away wireless general control



1. USE


Wireless general control, used to control leaving home/coming home scenes involving lights, roller shutters and connected sockets.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Fits on a piece of furniture (movable).

2. RANGE

Description	White	Champagne	Magnesium	Soft Alu
Additional wireless general control: Supplied with secable support frame, rocker plate and a battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used	5 742 06	5 742 33	5 742 24	5 742 15
to return to factory settings. Repositionable self-adhesive fixings (supplied).	374200	374233	3 / 12 21	374213


3. DIMENSIONS (mm)





Α	В	B'	С
82	116.5	82	12

4. OPERATION




Arrival scenario when pressed at the top: By default, switches on the connected sockets Can be customised with the Home + Control app

LED indicator:

- useful during installation

- when pressed, burst flashes red if the battery power is low

Leaving scenario when pressed at the bottom: By default, switches off all the lights in the installation Can be customised with the Home + Control app



RESET button used to return to factory settings

Connected Home/Away wireless general control

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies and/or liquids: IP 20

IP 40 mounted product

■ 5.2 Material characteristics

Rocker plate: ABS

Mechanism casing with grid: Fibreglass-reinforced (10%) PC

Halogen-free

UV resistant

Self-extinguishing: $650^{\circ}\,\text{C}$ / $30\,\text{s}$

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz

Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN)

Power level: < 100 mW

■ 5.4 Climate characteristics

Storage temperature: 0° C to $+ 45^{\circ}$ C Usage temperature: $+5^{\circ}$ C to $+ 45^{\circ}$ C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 742 06/15/24/33) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com

Created: 16/04/2018 **La legrand**

Cat. Nos: 5 742 06/15/24/33