


# **DOW Basic control devices - 1-way - 2-way - momentary switch**



# 1. USE

Axial switch control device for lighting and other control.

# 2. RANGE

Designation	Cat. No.	Related Cover Code	
1-way switch 10 AX - 250 V	K4001	□ KW01- KW01M2 - KW01A - KW01D KW01F - KW01X - KW01M2A KW01M2D - KW01M2F - KW01M2X	
2-way switch 10 AX - 250 V	K4003	KM01 - KM01M2 - KM01A - KM01D KM01F - KM01X - KM01M2A KM01M2D - KM01M2F - KM01M2X	
Momentary 1P switch 10 A - 250 V	K4005	■ KG01 - KG01M2 - KG01A - KG01D KG01F - KG01X - KG01M2A KG01M2D - KG01M2F - KG01M2X	


Colours code:

□ White

Sand

Black

# 3. OVERALL DIMENSIONS (mm)



А	В	с	D
45	22	32	2

# 4. CONNECTION

Screw clamps for all devices. Stripping length (rigid or flexible cables): 9 mm for screw terminals.

### **5. TECHNICAL CHARASTERISTICS**

#### 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D Impact test: IK 04

#### 5.2 Material characteristics

Material: Polycarbonate for mechanism case Halogen free. UV resistant. Self-extinguishing: - 850° C / 30 s for insulating parts holding live parts in place. - 650° C / 30 s for other parts made of insulating materials.

# ■ 5.3 Electrical characteristics

S.3 Electrical chara Voltage: 250 VAC Current: 10AX

#### ■ 5.4 Climatic charasteristics:

Storage and operating temperatures: - 5° C to + 35° C

# 6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichloroethylene.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

#### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufactoring. Refer to e.catalogue.