



Arteor™ 13A Multistandard Sockets with USB


Cat. No(s): 5 710 83/5 700 83/5 721 38/5 726 38
5 710 84/5 700 84/5 721 39/5 726 39
5 721 62/5 722 62/5 722 64/5 726 62



5 710 83/5 700 83
5 721 38/5 726 38



5 710 84/5 700 84
5 721 39/5 726 39



5 721 62
5 722 62/64
5 726 62


1. USE

Multistandard switched sockets with USB for recharging portables devices such as smartphones, tablets, Mp3 or MP4 players, loudspeakers, watches, game consoles, powerbanks, etc. Mechanism supplied with rocker plate, to be equipped with special plate. Support frame not needed Shuttered for child safety.

2. RANGE

Designation	White	Magnesium	Champagne	Alu
2P+E 1 gang switched + 1 USB Type-A (1 output Type-A)	5 721 38	5 726 38	5 710 83	5 700 83
2 x 2P+E 2 gang switched +1 USB Type-A + 1 USB Type-C (1 output Type-A - 1 output Type-C)	5 721 39	5 726 39	5 710 84	5 700 84
1G Multistandard switched socket + USB Type C (1 output Type-C)	5 721 62	5 726 62	5 722 62	5 722 64

3. DIMENSIONS (mm)



References	A	B	C	D
5 710 83/5 700 83/5 721 38/5 726 38	78.5	83.5	34.7	11.3
5 710 84/5 700 84/5 721 39/5 726 39	83.5	143.2	31.5	11.3
5 721 62/5 726 62/5 722 62/5 722 64	78.5	83.5	34.7	11.3

4. CONNECTION

Terminal types: with screw
Terminal capacity: 4 X 2.5 mm²
3 X 4 mm²
2 X 6 mm²
Recommended stripping length: 12 mm
Recommended terminal tightening torque: 0.5Nm

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Base: PP
Cover-plate: PC
Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Multistandard Socket:

Voltage: 127V~ Current: 15A
Voltage: 250V~ Current: 2.5/5/6/10/13/16A
Frequency: 50/60Hz

USB Chargers:

All values listed below are measured at an ambient temperature of + 25° and after 15 minutes of operation.

Type	1 USB (Type A)	1 USB (Type C)	2 USB (Type A+C)
Nominal input voltage	100-240V~	100-240V~	220-240V~
Nominal input frequency	50-60 Hz		
Power consumption	12 W	15 W	15 W
Maximum input current	300 mA	500 mA	300 mA
Maximum power consumption in standby	0.075 W		
Power average efficiency	79.94%	81.39%	81.39%
Nominal output voltage	5V---		
Maximum output current	2.4A	3.0 A	3.0 A*

No-load consumption and average energy efficiency: Level VI**

Protection class	II - Low voltage
------------------	------------------

5. TECHNICAL CHARACTERISTICS *(continued)*

* Note : shared on A and C output

** Note : European Regulation No. 278/2009 of 6 April 2009, Directive 2005/32/EC on eco-design requirements for AC/DC power supplies.

Note : To optimize the charging time of your device, ensure to turn it off during the charging phase.

5.3 Climatic characteristics

Storage temperatures: -20°C to +70°C

Operating temperatures: -5°C to +35°C

5.4 Mechanical characteristics

Impact test: IK02

Protection against solids & liquids: IP20

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.

Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform with installation and manufacturing standards.

Refer to e-catalogue.