


# Mémoire Metal style Mains voltage and ELV sockets

## Cat. Nos: AR-67137/38/39 - AR-67237/38/39



## 1. USE

Functions: 2 P+E + TV socket outlets, 2 P+E + RJ 45 socket outlets and 2 P+E + RJ 45 + TV socket outlets.


Mechanisms supplied with a protective cover.

## 2. RANGE

Mains voltage and ELV sockets					
AR-67137 AR-67237	<ul> <li>Brushed steel</li> <li>Brushed gold</li> </ul>	2 P+E + TV socket Consists of a 2 P+E socket - 16 A - 250 V~ and a single TV socket			
AR-67138 AR-67238	<ul> <li>Brushed steel</li> <li>Brushed gold</li> </ul>	2 P+E + RJ 45 socket Consists of a 2 P+E socket - 16 A - 250 V~ and a single TV socket			
AR-67139 AR-67239	<ul> <li>Brushed steel</li> <li>Brushed gold</li> </ul>	2 P+E + RJ 45 + TV socket Consists of a 2 P+E socket - 16 A - 250 V~ and a single TV socket			

**Note**: Other finishes and configurations are provided, see technical data sheet F02217EN/01.

## 3. DIMENSIONS (mm)



Cat. Nos	Α	В	С	D
67137 - 67237	80	222	41.5	5.5
67138 - 67238	80	151	39.5	3.5
67139 - 67239	80	151	41.5	5.5

## 4. ASSEMBLY

- Do not use an electric screwdriver to tighten the screws when assembling wiring accessories.
- Take care not to overtighten the visible screws when assembling Mémoire style wiring accessories:
- Risk of damaging the screw heads.
- Risk of the screwdriver slipping and permanently scratching the plate.
- Risk of the plate warping (bending), resulting in the plate not lying flat against the wall.
- Use a flat screwdriver (4 mm wide, 0.8 mm thick) for the screws supplied on the wiring accessory.
- ART d'Arnould electrical wiring accessories are supplied with long fixing screws which can be cut at several points to adapt the screw length to the box flush-mounting depth in the wall.

If ART d'Arnould wiring accessories are being mounted in thick surfaces such as tiles, marble, wainscot panelling with flush-mounting boxes chased deep into the wall, the whole screw length can be used to fix the wiring accessory.

If ART d'Arnould wiring accessories are being installed in walls with nonprojecting flush-mounting boxes (masonry walls, dry partitions), the screws which can be cut at several points to shorten the thread.

To protect the products, it is essencial to install them: once all surface coatings are completely dry, in a dry, non-agressive environment, indoors only.

It is recommended that you install the plates only after the wall coatings have been completely finished (paint, fabrics, etc.).

## 5.2 P+E SOCKET CONNECTION

#### Terminal type: auto

Terminal capacity: 2 x 2.5 mm<sup>2</sup> Stripping length: 13 mm

## 6. TECHNICAL CHARACTERISTICS OF 2 P+E SOCKETS

## ■ 6.1 Mechanical characteristics

Impact test: IK 02

Penetration of solid bodies and liquids: IP 20

## 6.2 Material characteristics

- Cover plates of socket outlets, Grey magnesium flat Surface (Mémoire brushed steel): PC
- Cover plates of socket outlets, Ivory flat Surface (Mémoire brushed gold): PC
- Plates: Brushed steel: brushed + galvanised with steel colour + varnish Brushed gold: brushed + galvanised with 24-carat gold + varnish
- Chrome screws
- Motor box: Zamac

Self-extinguishing:

 $850^\circ\text{C}/30$  s for insulating components holding live parts in place  $650^\circ\text{C}/30$  s for other insulating components

## 6. TECHNICAL CHARACTERISTICS OF 2 P+E SOCKETS (continued)


#### ■ 6.3 Electrical characteristics

Voltage: 250 V~ Current: 16 A Frequency: 50/60 Hz


## 6.4 Climate characteristics

Storage temperature: -  $10^{\circ}$ C to +  $70^{\circ}$ C Operating temperature: -  $5^{\circ}$ C to +  $35^{\circ}$ C

## 7. SINGLE TV SOCKET CONNECTION



#### ■ 7.2 Wiring instruction



## 8. TECHNICAL CHARACTERISTICS OF SINGLE TV SOCKETS

## ■ 8.1 Mechanical characteristics

Impact test: IK 02 Penetration of solid bodies and liquids: IP 20

#### ■ 8.2 Material characteristics • Plates: (see section 6.2)

Motor: • Box and cover: Zamak • Pin: Bronze • Screw: Zinc-plated steel


Sel-extinguishing: 650°C/30 s


## 8. TECHNICAL CHARACTERISTICS OF SINGLE TV SOCKETS (continued)


#### 8.3 Electrical characteristics

- Characteristic impedance: 75 Ohm
- $\bullet$  Female "F" screw-type SAT connector Ø 9.4 mm
- Shielding efficiency: Class A (class A shielding is necessary to prevent interference caused by using new 3 and 4 G telephone signals, as these unwanted signals can generate on-screen pixellation or adversely affect the soundtrack).
- Frequency bands: TV/SAT: 0 2400 MHz
- Attenuation: 1 dB maximum
- Compatible with remote power feeding
- 8.4 Climate characteristics (see section 6.4)

## 9. PERFORMANCE OF SINGLE TV SOCKETS








Created: 12/07/2017

### **10. STANDARD RJ 45 CONNECTION**

Takes the following plugs: RJ 11 (4 contacts), RJ 12 (6 contacts), RJ 45 (8 contacts UTP and 9 contacts FTP).

EIA/TIA 568 A and B dual colour code on terminals:

- FTP 9 contacts
- STP 9 contacts with 360° shielding







## Permissible conductors:


- Single-core: AWG 22 to 26

- Single-core: Awg 22 to 20


- Multicore: AWG 26

- Polyethylene conductor insulation: maximum Ø on insulation 1.58 mm

RJ 45 connectors are equipped with a locking nut. They do not require a special tool and can be re-wired if a mistake is made.



# This system makes it easy to spread pairs before fitting them onto the connector.



Spreading the cables ensures that a pair-breakage distance of 13 mm is kept between each pair.

Spreading pairs at  $90^\circ$  to the cable ensures the best possible performance.

## **10. TECHNICAL CHARACTERISTICS OF RJ 45 SOCKETS**

#### 10.1 Mechanical characteristics

Impact test: IK 02 Ingress of solids/liquids: IP 20

10.2 Material characteristics

#### • Plates: (see section 6.2)

Motor:

Contacts: gold/nickel, thickness of gold > 0.8 µm minimum Metal parts: bronze, nickel, platinum, gold Mechanism box: Polycarbonate PBT

Self-extinguishing: 650°C/30 s

#### 10.3 Electrical characteristics

Breakdown voltage  $\geq 1000 \text{ V}$ Contact resistance  $\leq 20 \Omega$ Insulation resistance  $\geq 500 \Omega$  under 100 V Vdc Compatible remote powering «PoE» up to 100 W (IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt) Tests are carried out with 2 simultaneous POE+ circuits for a minimum total power of 50 W.

#### ■ 10.4 Climate characteristics (see section 6.4)

#### **11. CARE**

Clean and dust using a soft, damp cloth (dampened with water) or wipes impregnated with a product containing less than 5% alcohol and anionic surfactant.

Caution: Always test before using other special cleaning products.

#### **Banned products:**

- Solvents, various essential oils, paint, or adhesive tape,
- Scouring powders (because are abrasive),
- Products containing bleach,
- Special products for stainless steel,
- Renovators (because they often contain abrasives and chemical agents),
- Splashes or fumes from floor, paint, or wood stripping products, etc.

## Caution:

Any mechanical attack or foreign object (screwdriver, etc.) striking the surface of the plate would damage the finish and therefore also the surface treatment.

## **12. STANDARDS AND APPROVALS**

Compliant with installation and manufacturing standards. See e.catalogue.