


# Valena™ Next Connected starter pack



# 1. USE

This pack enables you to create a connected installation in your home. It can be used to control lighting, roller shutters and electrical equipment plugged into connected sockets:

- using your smartphone and the Home + Control app
- using voice assistants
- from the general control at the entrance to your home

## **Comprises:**

-

## • A Control socket (Zigbee relay/WiFi)

Installation in 1-gang box 40 mm deep (minimum), instead of a standard socket outlet.

Claw and/or screw fixing.

Connected socket which can be controlled by a wireless lighting control and/or remotely via your smartphone.

The socket can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app.


One-piece mechanism (grid + mechanism).

- A wireless general control, used to control leaving home/coming home scenes involving lights, roller shutters and connected sockets.
- Fixes directly on the wall or screws onto a flush-mounting box. Multigang versions can be combined with other wiring accessories.

- Fits on a piece of furniture (movable).

Description	White	Alu	Black
Connected relay socket. Supplied complete with finishing plate and site protection covers. Equipped with a RESET button (hidden) used to return to factory settings.	7 418 00	7 418 30	7 418 60
Additional wireless general control. Supplied complete with battery, finishing plate. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 418 01	7 418 31	7 418 61


# 3. DIMENSIONS (mm)




6

7 418 01

References	Α	В	С	D
7 418 00/30/60	154	83	31.5	24.5







## **6. TECHNICAL CHARACTERISTICS**

#### 6.1 Mechanical characteristics

### Control socket:

Protection against impacts: IK 04

Protection against solid bodies and/or liquids: IP 40 assembled product

## **General control:**

Protection against impacts: IK 02 Protection against solid bodies and/or liquids: IP 20 without rocker plate and plate IP 40 for assembled product

#### ■ 6.2 Material characteristics of control socket

Plates: - ABS White (RAL 9003) polyglass appearance - ABS painted satin appearance for other colors Subplate: opalescent white PC

Cover plate: PC Mechanism casing: PC Support: Fibreglass-reinforced (20%) PC

Self-extinguishing: 850°C/30 s for insulating parts holding live parts in place. 650°C/30 s for the other insulating components.

#### 6.3 Material characteristics of general control

Plates: - ABS White (RAL 9003) polyglass appearance - ABS painted satin appearance for other colors Subplate: opalescent white PC

Mechanism casing with grid: Fibreglass-reinforced (10%) PC

Self-extinguishing: 650° C / 30 s

#### ■ 6.4 Electrical characteristics of control socket

Voltage: 110/230 V~ Current: 16 A Power: 3680 W max. Frequency: 50/60 Hz Standby consumption: 0.1 mA

WiFi technology 2.4 GHz (13 channels) - IEEE 802.11 b/g/n

ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN) Power level: < 100 mW

Range: 200 m of unobstructed space

10 m recommended between products indoors

6.5 Electrical characteristics of general control Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN) Power level: < 100 mW

#### 6.6 Climate characteristics

Storage temperature: 0° C to + 45° C Usage temperature: +5° C to + 45° C

Created: 29/11/2018

## 7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

The plates must not be painted.

Т 🕅 🔬

Take care to recycle the battery appropriately.

# 8. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

## 9. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 418 01/31/61 - 7 418 00/30/60) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: **www.legrandoc.com**