



Synergy™ Double pole socket outlets BS 13 A Metalclad

Cat. No(s): 7 338 60/61/70/71







7 338 71

1. USE

British standard double pole socket outlets, switched, delivered complete, for surface-mounting.


With safety shutters.

Fixing with screws.

2. RANGE

Double pole socket outlet - 1-Gang switched	7 338 60
Double pole socket outlet - 1-Gang switched with red led power indicator	7 338 61
Double pole socket outlet - 2-Gang switched	7 338 70
Double pole socket outlet - 2-Gang switched with red led power indicator	7 338 71

3. OVERALL DIMENSIONS (mm)



Cat. Nos	Α	В	С	D
7 338 60/61	86	86	46	10
7 338 70/71	86	146	46	10

4. CONNECTION

Type of terminals: with screws

Terminal capacity: $3 \times 2.5 \text{ mm}^2 - 2 \times 4 \text{ mm}^2 - 2 \times 6 \text{ mm}^2$

Stripping length: 12 mm

Compatible with flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 08

Penetration by solid bodies/liquids: IP 20

■ 5.2 Material characteristics

Rocker: PC - Color: White and red Front cover: PC - Color: White

Front plate and surface monting back box: Grey epoxy coated steel

Mechanism housing: PP - Color: Grey

Halogen free

UV resistant

Self-extinguishing:

- $+850^{\circ}$ C / 30 s for insulating parts holding live parts in place.
- $+650^{\circ}$ C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 13 A

Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth or soapy water.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.