


**Céliane™**  
**10 AX control**

Cat. No(s): 0 670 02




**1. USE**

General lighting control mechanism.  
 To be equipped with cover plate.

**2. RANGE**

Description	Cat. No.
2-way switch - Toggle mechanism Option to create a double 2-way switch in a 1-gang version	0 670 02

**3. DIMENSIONS (mm)**



A	B	C	D
45	45	24	8

**4. CONNECTION**

Type of terminals : automatic  
 Terminals capacity: 2 x 2,5 mm<sup>2</sup>  
 Stripping length: 12 mm

**5. WIRING**



**2-way switch connection**

**Non-standard drawing.**  
 To use only with 2 same mechanisms (Ref. 0 670 02).

**5. WIRING (continued)**

**Illumination function or signalling function**  
**Separate indicator**

Cat. No. 0 676 70 (230 Vac)



Cat. No. 0 676 70 (230 Vac)

**6. TECHNICAL CHARACTERISTICS**

■ **6.1 Mechanical characteristics**

Impact tests: IK 04  
 Penetration by solid bodies and liquids: IP 21 D

■ **6.2 Material characteristics**

Mechanism: PC  
 Colour: grey  
 Halogen-free

Self-extinguishing:  
 850°C/30 s for insulating parts holding live parts in place  
 650°C/30 s for other parts made of insulating materials

■ **6.3 Electrical characteristics**

Voltage: 250 V~  
 Current: 10 AX  
 Max. power for self-ballasted lamps: 100 W

■ **6.4 Climate characteristics**

Storage temperature: -10°C to +70°C  
 Operating temperature: -5°C to +35°C

---

#### **7. ACCESSORIES**

Signalling/Illuminated: 0 676 70 (230 V)

#### **8. STANDARDS AND APPROVALS**

Compliant with installation and manufacturing standards.  
See e-catalogue.