

1

87045 LIMOGES Cedex Telephone number: +33 5 55 06 87 87 – Fax: +33 5 55 06 88 88

Cat. N°(s): 4 159 19 / 20 / 21 / 22 / 28 / 29 / 30 / 31 / 32

DX³ STOP ARC 6000 A Phase + Neutral, neutral on right side

CONTENTS


PAGE

- 1. Description, use12. Range13. Overall dimensions14. Preparation Connection15. General characteristics36. Compliance and approvals6

1. DESCRIPTION - USE

Arc fault detection device integrated with thermal-magnetic circuit breaker (MCB) with contact position indication for the protection of a unitary electrical circuit. Reduction of the fire ignition risk in the electrical circuit, protection against short-circuits and overloads, isolation of electrical circuits.

Symbol:



Technology:

. Limiting device

. The Neutral contact closes before and opens after the Phase $\ensuremath{\mathsf{contact}}$

. The Phase pole provides protection and isolation for the Phase circuit

. The Neutral pole provides isolation for the Neutral circuit

2. RANGE

Polarity:

. 2 poles including 1 protected pole and 1 neutral pole

Width:

. 2 modules (36 mm)

Rated currents In:

. 6 / 10 / 13 / 16 / 20 A, C curve . 6 / 10 / 13 / 16 A, B curve


Magnetic tripping curves:

- . C curve (between 5 and 10 In)
- . B curve (between 3 and 5 In)

Rated voltage and frequency:

. 230 V ~, 50 Hz with standard tolerances

3. OVERALL DIMENSIONS



4. PREPARATION - CONNECTION

Mounting:


. On symmetrical EN 60.715 rail or DIN 35 rail

Operating position:

.Vertical Horizo

Horizontal Upside down









. From the bottom

4. PREPARATION - CONNECTION (continued)

Connection:

- . Terminals protected against direct contact IP20, wired device
- . Cage terminals, with release and captive screws

. Terminals fitted with shutters preventing a cable from beeing placed under the terminal, with the terminal partly open or closed . Alignment and spacing of the terminals permitting connection with the other products in the range via prong supply busbars

- . Terminal depth: 12 mm at the top and 13 mm at the bottom
- . Screw head: mixed, slotted and Pozidriv no. 2
- . Tightening torques:
 - Recommended: 1.6 to 2 Nm
 - Min.: 1.2 Nm
 - Max.: 2.8 Nm

Conductor type:

- . Copper cable or supply busbar
- . Cable cross-section

	Without ferrule	With ferrule	
Rigid cable	1 x 1.5 to 16 mm ² 2 x 1.5 to 6 mm ²		
Flexible cable	1 x 1.5 to 10 mm ² 2 x 1.5 to 4 mm ²	1 x 1.5 to 10 mm ²	

. Prong busbar, alone or with a flexible wire (without ferrule) 10 mm² or a connection terminal in the same terminal.

Recommended tools:

. For the terminals, screwdriver with 5.5 mm blade or Pozidriv no. 2 screwdriver


. For attaching or removing the DIN rail, screwdriver with 5.5 mm blade or Pozidriv no. 2 screwdriver

Manual actuation:

- . Ergonomic 2-positions handle
- . "I-ON": Device closed
- . "O-OFF": Device open

Contact status display:

- . By marking of the handle
- "O-OFF" in white on a green background = contacts open - "I-ON" in white on a red background = contacts closed
- Arc fault device status display:
- . By both indicator light and mechanical indicator



4. PREPARATION - CONNECTION (continued)

Indicator meaning code

Indicators state	meaning
- + -	No or incorrect electrical source or/and device switched off
+	Normal running: The circuit is monitored and protected by the arc fault device
- + -	Arc fault detected: The device tripped to avoid the risk of fire Installation has to be verified
+	Abnormal running: The circuit is not protected by the arc default device.

Insulation tests:

. Very important:

Disconnect output wires and handle must be OFF.

Arc fault detection tests:

. The DX³ STOP ARC is equipped with an auto-test function running continuously. The LED indicates if an abnormal running is detected.

Sealing:

. Possible in the open or closed positions


Labelling:

. Circuit identification with a label inserted in the label holder.









Updated on: 28/06/2022




5. GENERAL CHARACTERISTICS

Neutral earthing system:

. IT, TT, TN

Marking on the front side:



. The upstream and downstream terminals of the neutral pole are marked with an "N" moulded close to the screw heads.

Electrical diagram

Minimum operating voltage:

Rated voltage

- . U = 70 V (without auxiliaries)
- . U = 95 V (with auxiliaries)

Maximum operating voltage:

. U = 250 V

Arc fault detection device:

- . Compliant with standard IEC/EN 62606:
- . Fully Integrated with a MCB
- . Protects against parallel and series arc fault
- . Protects against earth arc fault

State indicators integrated in the device (see chapter Arc fault device status display)

Breaking capacity on one single pole (phase pole): . In accordance with Icn1 EN60898-1: 4.5 kA at 230 V ~

Breaking capacity:

Standard	Breaking capacity	Voltage between poles	Breaking capacity
EN/IEC	lcs	230 V	6 kA
60898-1	lcn	230 V	6 kA

5. GENERAL CHARACTERISTICS (continued)

Installation requirements:

...stanation requirements: . The device is intended for unitary circuit protection as per the installation and operating conditions defined by the product standard and shall not be installed upstream of a group of circuit breakers or multiple circuits.

Isolation distance:

. The distance between the contacts is greater than 5.5 mm with the handle in the open position.

. The DX³ STOP ARC is suitable for isolation in accordance with standard EN/IEC 60898-1.

Insulation voltage:

. Ui = 400 V in accordance with standard EN/IEC 60898-1

Pollution degree: . 2 in accordance with standard EN/IEC 60898-1

Dielectric strength: . 2,000 V on input and handle off

Rated impulse withstand voltage:

. Uimp = 4 kV

Protection class (protection degree):

. Terminals protected against direct contact. Protection class against solid objects and liquids (wired device): IP20 in accordance with standards IEC 529 - EN 60529 and NF 20-010

- . Front panel protected against direct contact: IP40
- . Class II in relation to metallic conductive parts

. Protection class against mechanical impacts IK02 in accordance with standard EN 62262.

Plastic materials:

. Polyamide and P.B.T.

Enclosure heat and fire resistance:

- . Resistance to glow wire tests at 960°C, in accordance with standard EN/IEC 60898-1
- . Classification V2. in accordance with standard UL94

Higher heating potential:

. The heat potential is assessed at: 2.60 MJ

Closing and opening force via the handle:

- . 4 N on opening
- . 10 N on closing

Mechanical endurance:

- . Compliant with standard EN/IEC 60898-1 & EN/IEC 62606
- . Tested with 20,000 operations

Electrical endurance:

- . Compliant with standard EN/IEC 60898-1 & EN/IEC 62606
- . Tested with 10,000 operations with load (In x Cos (0.9))

Sinusoidal vibration resistance in accordance with IEC 60068.2.6:

. Axes: x - y - z

- . Frequency: 10 to 55 Hz
- . Acceleration: $3g(1g = 9.81m.s^{-2})$

Resistance to tremors:

. In accordance with standard EN/IEC 60898-1

Ambient temperatures:

. Operation: from - 25°C to + 40°C . Storage: from - 40°C to + 70°C

5. GENERAL CHARACTERISTICS (continued)

EMC Compatibility:

The design of DX³ STOP ARC with its intelligent signal analysis of the power grid avoids any interference with PLC signal.

Tests according to IEC 61000 guarantee electromagnetic compatibility with other devices on the power grid.

Packaged volume:

Packaging	Volume (dm ³)		
Per 1	0.360		

Average unit weight per catalogue number:

. 0.19 kg

Derating of DX³ STOP ARC function of the number of devices placed side by side:

When several MCBs are installed side by side and operate simultaneously, the heat dissipation of one pole is limited. This results in an increased operating temperature for the circuit breakers which may cause nuisance tripping. Applying the following coefficients to the operating currents is recommended.

Number of MCBs side by side	Coefficient
2 - 3	0.9
4 - 5	0.8
6 - 9	0.7
≥ 10	0.6

These values are given in the IEC 60439-1 recommendation and NF C 63421 and EN 60439-1 standards.

In order to avoid having to use these coefficients there must be good ventilation and the devices must be kept apart using the spacing elements Cat. No. 4 063 07 (0.5 module).

Derating of DX³ STOP ARC in the event of use with fluorescent tubes:

LEDS and electronic or ferromagnetic ballasts provide a high inrush current for a very short time. These currents are liable to cause tripping of the DX3 STOP ARC.

The maximum number of ballasts per MCB stated by the lamp and ballast manufacturers in their catalogues should be taken into account during installation.

Impact of height:

	≤2,000 m	3,000 m	4,000 m	5,000 m
Dielectric strength	2,000 V	1,750 V	1,500 V	1,250 V
Maximum operating voltage	230 V	230 V	230 V	230 V
Derating at 30°C	none	none	none	none

Power dissipated:

. with In/Un

Rated current	6 A	10 A	13 A	16 A	20 A
Power (W) dissipated	3.1	2.4	4.6	5.8	6.6

5. GENERAL CHARACTERISTICS (continued)

Derating of DX³ STOP ARC depending on the ambient temperature:

. The nominal characteristics of a circuit breaker are modified depending on the ambient temperature which prevails in the cabinet or enclosure where the MCB is located.

. Reference temperature: 30°C in accordance with standard EN/IEC 60898-1.

In (A)	-10°C	0°C	10°C	20°C	30°C	40°C	50°C	60°C	70°C
6	7.2	6.9	6.6	6.3	6	5.7	5.4	5.1	4.8
10	12	11.5	11	10.5	10	9.5	9	8.5	8
13	15.6	14.95	14.3	13.65	13	12.35	11.7	11.05	10.4
16	19.2	18.4	17.6	16.8	16	15.2	14.4	13.6	12.8
20	24	23	22	21	20	19	18	17	16



side

6. COMPLIANCE AND APPROVALS

In accordance with standards:

. IEC/EN 60898-1

. IEC/EN 62606

Usage in special conditions:

. Category C in accordance with the classification defined in Appendix Q of standard IEC/EN 60947-1.

. Category C = Environment subject to temperature (-25°C to +70°C), humidity.

Respect for the environment – Compliance with European Union Directives:

. Compliance with Directive 2002/95/EC of 27/01/03 known as "RoHS" which provides for a restriction on the use of dangerous substances such as lead, mercury, cadmium, hexavalent chromium and polybrominated biphenyl (PBB) and polybrominated diphenyl ether (PBDE) brominated flame retardants from 1st July 2006

. Compliance with the Directive 91/338/EEC of 18/06/91 and decree 94-647 of 27/07/04

Plastic materials:

. Halogen free plastic materials.

. Labelling of parts compliant with ISO 11469 and ISO 1043.

Packaging:


. Design and manufacture of packaging compliant with decree 98-638 of 20/07/98 and Directive 94/62/EC



Cat. N°(s): 4 159 19 / 20 / 21 / 22 / 28 / 29 / 30 / 31 / 32


7. CURVES

Arc tripping time curve




7. CURVES (continued)

Thermal-magnetic tripping curve range typical of B and C curve DX³ STOP ARC:




7. CURVES (continued)

Average thermal-magnetic tripping curves range typical of B curve DX³ STOP ARC:




7. CURVES (continued)

Average thermal-magnetic tripping curves range typical of C curve DX³ STOP ARC



7. CURVES (continued)

Current limiting curves:



Icc = Prospective short-circuit symmetrical current (rms value in kA)

lp = Maximum peak value (in kA)

1 = Short-circuit rms currents (max. peak)

2 = Unlimited peak currents (max.), corresponding to power factors shown above (0.15 to 0.9)

Technical data sheet: F02541EN/05


Updated on: 28/06/2022

Created on: 8/11/2017

L¹ legrand

7. CURVES (continued)

Thermal stress limiting curves:



 $I^{2}t$ = limited thermal stress (in A s)²

Technical data sheet: F02541EN/05

Updated on: 28/06/2022

Created on: 8/11/2017

L7 legrand

8. AUXILIARIES AND ACCESSORIES

Wiring accessories:

- . Supply busbar:
- HX³ single-pole universal supply busbar (Cat. No. 4 049 26 / 37)
- . Connection terminals (cat. No. 4 049 05)
- . Sealable screwcover (cat. No. 4 063 04)

Signalling auxiliaries:

- . Auxiliary contact (0.5 module, Cat. No. 4 062 50)
- . Fault signalling contact (0.5 module, Cat. No. 4 062 52)
- . Auxiliary contact that can be changed into fault signalling contact (0.5 module, Cat. No. 4 062 56)
- . Auxiliary contact + fault signalling contact that can be changed into 2 auxiliary contacts (1 module, Cat. No. 4 062 64)

Control auxiliaries:

Only possible with a signalling auxiliary positioned between the control auxiliary and the DX³ STOP ARC

- . Shunt trip (1 module, Cat. No. 4 062 76 / 78)
- . Under voltage release (1 module, Cat. No. 4 062 80 / 82)
- . Autonomous shunt trip release for N/C push-button (1.5 module, Cat. No. 4 062 87)
- . Power Overvoltage Protection (1 module, Cat. No. 4 062 86)

Possible combinations of auxiliaries and the DX³ STOP ARC:

- . The auxiliaries are installed to the left of the DX³ STOP ARC
- . Maximum number of auxiliaries = 2
- . Maximum number of 1 module signalling auxiliaries = 1

Locking options:

. Via padlock 5 mm in diameter (Cat. No. 4 063 13) or padlock 6 mm in diameter (Cat. No. 0 227 97) and padlock support (Cat. No. 4 063 03)

Installation software:

. XL PRO³

