


**Mosaic™**

Cat. No(s): 0 771 17L/26L/32/33/35 - 0 787 04

**Antimicrobial\* 2P+E Flush socket outlets  
 French/Belgian standard**



0 771 26L

**1. USE**

Shuttered 2P+E Flush socket outlets.  
 Easy to clean and prevent accumulation of dirt.  
 Flush or surface-mounting.  
 For installation in flush-mounting box 40 mm deep (minimum recommended).


**Antimicrobial\* socket outlets:**

Products are made of silver-ion based antimicrobial\* material.  
 This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical destruction).  
 Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc).  
 These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

**2. RANGE**

Description	White	Red	Green	Orange
Antimicrobial* Surface 2P+E 2 modules	0 771 32	0 771 33	0 787 04	0 771 17L
Antimicrobial* Surface 2P+E including light - 2 modules	0 771 35	0 771 26L	-	-

**3. DIMENSIONS (mm)**



A	B	C	D
45	45	38.5	8.5

**4. CONNECTION**

Type of terminals: automatic  
 Number of terminals: 3 inputs, 3 outputs  
 Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
 Stripping length: 12 mm

**5. TECHNICAL CHARACTERISTICS**

■ **5.1 Mechanical characteristics**

Penetration by solid/liquid matter: IP 40 for assembled product  
 Impact resistance: IK 04

■ **5.2 Material characteristics**

Mechanism casing: PC  
 Cover plate: White RAL 9003 ABS + PC + antimicrobial\* treatment  
 Red - Green - Orange PC + antimicrobial\* treatment

Halogen-free  
 UV-resistant

Self-extinguishing:  
 850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

■ **5.3 Electrical characteristics**

Current: 16 A  
 Voltage: 250 V~

■ **5.4 Climate characteristics**

Usage temperature: -5°C to +35°C  
 Storage temperature: -10°C to +70°C

**6. CARE**

Clean the surface with a cloth.  
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

■ **6.1 Resistance to cleaning products**

Hexane (NF C 61-314), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

■ **6.2 Resistance to hospital-grade cleaning products**

Anios, Surfanios, Bactylisine, diluted hydrogen peroxide (35%).

**Caution:** Always test before using other special cleaning products.

## Antimicrobial\* 2P+E Flush socket outlets French/Belgian standard

---

### 7. ACCESSORIES

0 676 64: Indicator light - 2.4 mA

### 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.  
See e-catalogue.

\* Contains silver ions that limit the development of bacteria on the surface.