



Mosaic™ Antimicrobial* Mosaic Link 2P+E Flush socket outlets

Cat. No(s): 0 771 48L/58L/88L/95L



0 771 58L



0 771 88L

1. USE

Modular shuttered 2P+E Flush socket outlets that can be joined together, for installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions, trunking and flush-mounting boxes with 50 mm recommended depth.

Easy to clean and prevent accumulation of dirt.

Mosaic Link socket outlets can be added with connection accessory Cat. No. 0 771 00L.

Usage restriction:

In plastic trunking, the mechanical strength of an assembly made up of Mosaic Link socket outlets is limited to 4 recesses maximum.

Antimicrobial* socket outlets:

Products are made of silver-ion based antimicrobial* material. This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical destruction).


Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc).

These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

2. RANGE

Mosaic Link 2P+E Flush socket outlets at a 45° angle French standard - 2 modules	White antimicrobial*	Red antimicrobial*
2P+E Flush socket outlet	0 771 58L	-
2P+E Flush socket outlet including light With hospital marking for Cat. No. 0 771 95L	0 771 48L	0 771 95L
Tamperproof 2P+E Flush socket outlet	-	0 771 88L

3. DIMENSIONS (mm)



4. CONNECTION

Type of terminals: automatic

Number of terminals: 3 inputs, 3 outputs

Terminal capacity: 2 x 2.5 mm²

Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Penetration by solid/liquid matter: IP 41 for assembled product

Impact resistance: IK 07

■ 5.2 Material characteristics

Mechanism casing: PC

Cover plates: White RAL 9003 ABS + PC + antimicrobial* treatment
 Red ABS + PC + antimicrobial* treatment

Halogen-free

UV-resistant

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Current: 16 A

Voltage: 250 V~

■ 5.4 Climate characteristics

Usage temperature: -5°C to +35°C

Storage temperature: -10°C to +70°C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

■ 6.1 Resistance to cleaning products

Hexane (NF C 61-314), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

■ 6.2 Resistance to hospital-grade cleaning products

Anios, Surfianios, Bactylisine, diluted hydrogen peroxide (35%).

Caution: Always test before using other special cleaning products.

Antimicrobial* Mosaic Link 2P+E Flush socket outlets

7. ACCESSORIES



Mosaic Link connection accessory.
Used to link 2 socket outlets or 2 socket blocks,
either Mosaic Link or Soluclip for snap-on
trunking.

0 771 00L

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e-catalogue.

*Contains silver ions that limit the development of bacteria on the surface.