


Valena™ Allure Connected 1-gang ON/OFF wireless control for lighting and sockets

Cat. No(s): 7 525 85 - 7 526 85 - 7 527 85 - 7 528 85 - 7 529 85



1. USE

Wireless control for one ON/OFF light function or connected socket.
 Controls micromodule products, connected sockets and connected dimmer switches.
 Can be used as a two-way switch or to control a lighting group.


- Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

Can be combined with 20 connected switches with dimming option or connected sockets.

2. RANGE


Description	White	Ivory	Aluminium	Black	Pearl
Wireless lighting and socket control, for an ON/OFF, dimmer, centralisation function. Supplied complete with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 525 85	7 526 85	7 527 85	7 528 85	7 529 85

3. DIMENSIONS



A	B	C
90	90	14

4. OPERATION



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
Protection against solid bodies/liquids:
- IP 20 without plate and rocker plate
- IP 40 for assembled product

■ 5.2 Material characteristics

Plate: ABS
Sub-plate: PC
Rocker plate: ABS
Mechanism casing with grid: Fibreglass-reinforced (10 %) PC
Halogen-free
UV resistant
Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
Battery life: 8 years for 10 activations a day
ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz
Power level: < 100 mW
Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN)

■ 5.4 Climate characteristics

Usage temperature: + 5° C to + 45° C
Storage temperature: 0° C to + 45° C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.
Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 525 85 - 7 526 85 - 7 527 85 - 7 528 85 - 7 529 85) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com