


**Mosaic™**  
**Antimicrobial\* 2 P+E Flush socket outlets**  
**Franco-Belgian standard**

Cat. No(s): 2 781 12L/26L/41L/46L/47L



2 781 12L

**1. USE**

2 P+E surface socket outlet for installation in flush-mounting box 40 mm deep (minimum recommended, surface-mounting box, workstation kit, floor box, column module, desktop multi-outlet extension and trunking. Facilitates cleaning and avoids the accumulation of dirt.

**Antimicrobial\* sockets:**

These products are made of silver-ion based antimicrobial\* material. This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical, destruction).


Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc.) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc.).

These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

**2. RANGE**

	White	Red	Green	Orange
Antimicrobial* Surface 2P+E 2 modules	-	2 781 41L	2 781 46L	2 781 47L
Antimicrobial* Surface 2P+E including light - 2 modules	2 781 12L	2 781 26L	-	-

**3. DIMENSIONS (mm)**



A	B	C	D
45	45	38.5	8.5

**4. CONNECTION**

Type of terminals: automatic  
 Number of terminals: 3 inputs, 3 outputs  
 Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
 Stripping length: 12 mm

**5. TECHNICAL CHARACTERISTICS**

■ **5.1 Mechanical characteristics**

Protection against solid bodies and liquids: IP 41  
 Protection against impacts: IK 04

■ **5.2 Material characteristics**

Bases: PC  
 Covers: PC + antimicrobial\* treatment  
 White RAL 9003  
 Red RAL 3020  
 Green RAL 2003  
 Orange

Halogen-free  
 UV-resistant

Self-extinguishing:  
 850°C/30 s for insulating parts holding live parts in place.  
 650°C/30 s for other parts made of insulating materials.

■ **5.3 Electrical characteristics**

Voltage: 250 V~  
 Current: 16 A

■ **5.4 Climatic characteristics**

Storage temperature: - 10°C to + 70°C  
 Operating temperature: - 5°C to + 35°C

**6. CLEANING**

Surface cleaning with a cloth.  
 Do not use: acetone, tar remover, trichloroethylene.

■ **6.1 Resistance to the cleaning products:**

Hexane (NF C 61-314), Methylated spirit, Soapy water, Diluted ammonia, Pure bleach diluted to 10%, Window-cleaning products, Pre-impregnated wipes.

■ **6.2 Resistance to hospital-grade cleaning products:**

Anios, Surfanios, Bactylisine, hydrogen peroxide (35%).

**Caution:** Always test before using other special cleaning products

## Antimicrobial\* 2 P+E Flush socket outlets Franco-Belgian standard

---

### 7. ACCESSORIES

0 676 64: Indicator light - 2.4 mA

### 8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
See e. catalogue.

\* Contains a silver compound to antagonize the growth of bacteria on the surface.