



Epure Style Blanking plates

Cat. No(s): AR68061/62
 AR68161/62 - AR68261/62 - AR68361/62 - AR68461/62



AR68x61



AR68x62

1. USE

Blanking plates.
 Flush-mounting.
 Fixing with screws.

2. RANGE

One-gang blanking plates


AR68061	<input type="radio"/> Configured Cat. No
AR68161	<input type="radio"/> Brushed steel
AR68261	<input type="radio"/> Brushed gold
AR68361	<input type="radio"/> Satin white
AR68461	<input checked="" type="radio"/> Matt black

Two-gang blanking plates

AR68062	<input type="radio"/> Configured Cat. No
AR68162	<input type="radio"/> Brushed steel
AR68262	<input type="radio"/> Brushed gold
AR68362	<input type="radio"/> Satin white
AR68462	<input checked="" type="radio"/> Matt black

Note: Other finishes and styles are provided, see technical data sheet F02217EN.

3. OVERALL DIMENSIONS (mm)



Cat. Nos	A	B	C	D
AR68x61	86	86	15,5	4
AR68x82	86	146	15	4

4. DISMANTLING

The plates can be dismantled by inserting the tip of a screwdriver in a purpose-designed notch on the sides of the plate and using it as a lever to unclip it from the fixing points.
 Once the plate has been lifted off the wall slightly, just slide your fingers between the plate and the wall to gently remove the plate.
 Take care not to pull too hard on the plate, to avoid breaking the fixing clips.

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Impact tests: IK 02
 Penetration by solid bodies/liquids: IP 20

5.2 Material characteristics

• Decorative brass:
 AR68161 - AR68162 - AR68261 - AR68262

• Brass + paint:
 AR68361 - AR68362 - AR68461 - AR68462

Halogen-free
 UV-resistant

Self-extinguishing:
 850°C/30 s for insulating components holding live parts in place.
 650°C/30 s for other insulating components.

J 5.3 Climate characteristics

Storage temperature: - 10°C to + 70°C
 Usage temperature: - 5°C to + 35°C

6. CARE

6.1 Installation

To protect the products, it is essential to install them:
 - once all surface coatings are completely dry,
 - in a dry, non-aggressive environment,
 - indoors only.

It is recommended that you install the plates only after the wall coatings have been completely finished (paint, fabrics, etc.).

6.2 Instructions

Clean and dust using a soft, damp cloth (dampened with water) or wipes impregnated with a product containing less than 5% alcohol and anionic surfactant.

6. CARE (continued)

■ 6.3 Banned products

- solvents, various essential oils, paint, or adhesive tape,
- scouring powders (because are abrasive),
- products containing bleach,
- special products for stainless steel,
- renovators (because they often contain abrasives and chemical agents),
- splashes or fumes from floor, paint, or wood stripping products, etc.

Caution: Always test before using other special cleaning products.
Any mechanical attack or foreign object (screwdriver, etc.) striking the surface of the plate would damage the finish and therefore also the surface treatment.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e.catalogue.