


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Niloé^{™ 「sélection}」 Rotary dimmer 300 W RLC + LEDs



1. USE

Rotary dimmer for all types of lamps.

Can be associated with one or several push buttons, for ON/OFF or dimming control.

Integrates memory level function : the light switches ON the same level it has been switched OFF.


Soft-start and soft-stop lighting (2 s).

Mechanisms to be equipped with plates.

Screw or claw mounting.

2. RANGE


Description	Aluminium	Antharcite	Smoked grey	Pearl
Rotary dimmer 300 W - 2-wires	7 621 88	7 622 88	7 623 88	7 624 88



5. INSTALLATION


Simple







With push buttons



6. TECHNICAL CHARACTERISTICS (continued)

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mecanical characteristics

Protection against solid bodies and liquids: IP 40 Protection against impact: IK 02

■ 6.2 Material characteristics

Polyglass appearance

Material: - Front cover: ABS

- Halogen free

- UV resistant

Material of the support: - Polycarbonate grey RAL 7037 + 10 % glass fiber - Halogen free

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place

+ 650° C / 30 s for other parts made of insulating materials.

6.3 Electrical characteristics

Voltage: 100 to 240 V~ Frequency: 50-60 Hz

Standby consumption: 0.2 W


6.4 Climatic characteristics

Storage temperature : - 10° C to + 70° C Use temperature: 0° C to + 40° C

• Load table												
		R		L		C/L						
		P		(*) + @	(*)	+ LED+++			LED			
		-¤ָ-	-¤-			120						
200 V / 240 V	Max.	300 W	300 W	300 VA	300 VA	300 VA	300 VA	75 W or 10 lamps max.	75 W or 10 lamps max.			
	Min.	5 W	5 W	5 VA	5 VA	5 VA	5 VA	5 W	5 W			
100 V / 200 V	Max.	150 W	150 W	150 VA	150 VA	150 VA	150 VA	37 W or 10 lamps max.	37 W or 10 lamps max.			
	Min.	5 W	5 W	5 VA	5 VA	5 VA	5 VA	5 W	5 W			

(*)Use only with transformers designed to function with electronic switches.

• Setting C or L



7. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. Refer to e. catalogue.

Created: 15/10/2020