


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel.: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

Plexo[™] Connected 2P+E socket - Waterproof




1. USE

Connected socket which can be controlled by a wireless lighting control and/or remotely via a smartphone and/or via voice assistant. Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app. IP55 weather proofness allows this product in rooms that are humid or dusty (cellar, garage,...).


Built-in protection against electrical overloads, for increased safety. Fixes directly on the wall.

2. RANGE

Description	Grey
IP55 connected 2P+E socket outlet, german standard. With activity and identification LED indicator and RESET button (hidden) used to return to factory settings. Supplied complete with surface-mounted housing.	0 697 96



4. COMPOSITION



5. CONNECTION


• 2P+E socket:

Terminal type: automatic Terminal capacity: 2 x 2.5 mm² Stripping length: 11 mm

Module:

Terminal type: with screws Terminal capacity: 2 x 2.5 mm² Stripping length: 7 mm

6. OPERATION



7. TECHNICAL CHARACTERISTICS

7.1 Mechanical characteristics

Protection against impacts: IK07 Protection against solid bodies and/or liquids: IP55

7.2 Material characteristics

Module cover: ABS Box, support : PP Front plate, flap: ABS Entry gland, cover plate: PP + SEBS

Halogen-free UV-resistant

Self-extinguising: 850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

7.3 Electrical characteristics

Voltage: 110/230 V~ Curent: 16 A Power: 3680 W max. Standby consumption: 0.1 mA

Frequency bands: 2.4 GHz to 2.4835 GHz Power level: < 100 mW Range: 200 m of unobstructed space 10 m recommended between products indoors

7.4 Climate characteristics

Storage temperature: $0^{\circ}C$ to + $45^{\circ}C$ Usage temperature: $5^{\circ}C$ to + $45^{\circ}C$

8. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichloroethylene.

Resistance to the cleaning products: Hexane (EN 60669-1), methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

This product must not be painted.

9. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 697 93) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: **www.legrandoc.com**