


Mallia™ Senses 32A DP Switch

Cat. No(s): 2 810 74 MW - 2 810 74 MG - 2 810 74 MB
2 810 74 DS - 2 810 74 CH - 2 810 74 DB
2 810 74 BA - 2 810 74 BB - 2 810 74 BC



2 810 74 XX

1. USE

High capacity double pole switches for the control of fixed appliances eg. cooker ovens, shower or air-conditioning units, Version available with LED "power on" indicator.
(Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE


Designation	Cat. No.
1G 1W 32A Double Pole SWITCH RED INDICATOR	2 810 74 XX

Colours

-Front: MW/MG/MB/DS/CH/DB/BA/BB/BC
-Rear: grey

2 81X XX MW	Matt White
2 81X XX MG	Matt Grey
2 81X XX MB	Matt Black
2 81X XX DS	Dark Silver
2 81X XX CH	Champagne
2 81X XX DB	Dark Bronze
2 81X XX BA	Brushed Aluminium
2 81X XX BB	Brushed Black
2 81X XX BC	Brushed Champagne

3. DIMENSIONS (mm)



References	A	B	C	D
2 810 74 XX	86	86	34	22.9

4. CONNECTION

Types of terminals: with screws
Terminal capacity: 2 × 6 mm²
1 × 10 mm²
Recommended stripping length: 22 mm
Recommended screwdriver size: <4 mm flat blade

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Rocker: PC
Frame: Steel
Base: PC
Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Voltage: 250V~
Current: 32A

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C
Operating temperatures: -5°C to +50°C

5.4 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP20

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.
Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform to BS EN 60669-1 ; MS/IEC 60669-1; BS4177.