



Mosaic™ Franco-Belgian socket outlets

Cat. No.(s): 2 781 14L/15L/49L



2 781 14L



2 781 49L

1. USE

2 P+E socket outlets Franco-Belgian standard.
 The mechanism can be flush-mounted or surface-mounted.
 To be equipped with plates.

Antimicrobial* sockets:

These products are made of silver-ion based antimicrobial* material.
 This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical, destruction).


Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc.) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc.).

These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

2. RANGE

Description	White	Red
Tamperproof 2 P+E socket antimicrobial* with indicator light	-	2 781 15L
2 P+E socket with flush cover	2 781 49L	-
Tamperproof 2 P+E Socket	-	2 781 14L

3. OVERALL DIMENSIONS (mm)



Cat. Nos	A	B	C	D
2 781 49L	45	45	38.5	8.5
2 781 14L/15L	45	45	37	9

4. CONNECTION

Automatic terminals:

Cat. No: 2 781 49L
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 12 mm

Screw terminals:

Cat Nos: 2 781 14L/15L
 Terminal capacity: 2 x 2.5mm²
 Tripping length: 9 mm - Screwdriver: 4 mm flat-blade

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04 (mounted product)
 IK 07 for Cat. No 2 781 49L (mounted product)
 Protection against solid bodies and liquids: IP 41

■ 5.2 Material characteristics

Base: PC
 Cover: PC White RAL 9003
 PC Red RAL 3020
 Cat. No 2 781 15L: PC + antimicrobial treatment*.

Halogen-free
 UV-resistant

Self-extinguishing:

850°C/30 s for insulating parts holding live parts in place.
 650°C/30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250 V~
 Current: 16 A

■ 5.4 Climatic characteristics

Storage temperature: - 10°C to + 70°C
 Operating temperature: - 5°C to + 35°C

6. CLEANING

Surface cleaning with a cloth.
 Do not use: acetone, tar remover, trichloroethylene.

■ 6.1 Resistance to the cleaning agents:

Hexane (NF C 61-314), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning substances, Pre-impregnated wipes.

■ 6.2 Resistance to type cleaning hospital:

Anios, Surfanios, Bactylisine, hydrogen peroxide (35%).

Caution: Always test before using other special cleaning products

7. ACCESSORIES

Indicator light for:

Socket outlets	LED indicator with 2 wires to cable
2 781 15L	0 676 64 (230 V - 2.4 mA)

Tamperproof for:

Socket outlet	Tamperproof insert
2 781 14L 2 781 15L	0 502 99

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
See e. catalogue.

* Contains a silver compound to ontagonize the growth of bacteria on the surface.