



Mosaic[™] Pushbuttons

Cat. No(s): 2 780 30L/40L



2 780 30L



2 780 40L

1. USE


Depending on the wiring, can become a two-way pushbutton. A mechanism allows you to create an LED or standard function. Flush or surface-mounting.


To be fitted with finishing plates.

2. RANGE

Description	White
1-module pushbutton Its mechanism allows you to create an LED or standard function. Can become illuminated with plug-in indicator Cat. No. 0 676 86L (230 V) or Cat. No. 0 676 87L (12, 24, 48 V).	2 780 30L
2-module pushbutton Its mechanism allows you to create an LED or standard function. Can become illuminated with plug-in indicator Cat. No. 0 676 86L (230 V) or Cat. No. 0 676 87L (12. 24. 48 V)	2 780 40L

3. DIMENSIONS (mm)





Cat. Nos.	Α	В	С	D
2 780 30L	45	22.5	36.5	12.5
2 780 40L	45	45	36.5	12.5

4. CONNECTION

Automatic terminals Terminal capacity: 2 x 2.5 mm² Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid/liquid matter: IP 31 D

■ 5.2 Material characteristics

Mechanism casing: PC

Rocker plate: White RAL 9003 ABS + opalescent white PC

Halogen-free

UV-resistant

Self-extinguishing:

 850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 6 A

■ 5.4 Climate characteristics

Storage temperature: -10°C to $+70^{\circ}\text{C}$ Usage temperature: -5°C to $+35^{\circ}\text{C}$

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: Hexane (EN60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. ACCESSORIES

Easy-Led plug-in indicators with white LEDs.

Clip onto the front of the mechanism by removing the rocker plate.

Illuminated lights			
0 676 86L	230 V~ - 0.041 W		
0 676 87L	12/24/48 V~ - 0.006 W/0.033 W/0.153 W		

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.