


Céliane™

Cat. No(s): 1 991 34/35

Connected extension pack "with Netatmo" Color ambience




Color ambience
wireless control

Repositionable
adhesives



Sticker



Plate



Ledvance Smart+
bulb



Connection terminal

1. USE

This product enables you to complete a connected installation in your home.

For remote control of your colors ambience lightings and electrical appliances:

- from your Ambiance Colours wireless control
- using your smartphone and the Home + Control app,
- using voice assistants.

2. RANGE

Designation	White	Titanium
Color ambience connected expansion pack	1 991 34	1 991 35

Includes:

• A wireless control for color variation

3 atmospheres to choose from (I - II - III) to be configured in the Home + Control App.

With LED indicator (configuration) and RESET button (hidden) used to return to factory settings.

Allows control of connected multi-color lights.

Controls Zigbee 3.0 certified smart bulbs and lights (such as Ledvance Smart+ Zigbee, Philips HUE and many more).

Can be used as a two-way switch or to control a lighting group.

• Fixes directly on the wall or screws onto a flush-mounting box.

Multi-gang versions can be combined with other wiring accessories.

• Fits on a piece of furniture (movable).

Can control up to 20 zigbee 3.0 connected lights.

• A finishing plate

• A multicolour dimmable Ledvance smart+ bulb - with wireless control via app.

• A connection terminal (Cat. No. 0 343 23) for 3 wires for an existing switch.

• A sticker for an existing switch.

3. CONNECTION


Connection terminal for 3 wires:

Type of terminals: automatic

For rigid wires from 0.75 to 2.5 mm²



Stripping length: 11 mm

4. DIMENSIONS (mm)



	A	B	C
Wireless control	74	74	13
Plate	82	90	8.5

5. OPERATION



RESET button
used to return to factory mode

Connected extension pack "with Netatmo"
Color ambiance

6. TECHNICAL CHARACTERISTICS

■ 6.1 CONNECTED WIRELESS CONTROL

■ 6.1.1 Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies and liquids: IP 20

IP 40 assembled product

■ 6.1.2 Material characteristics

Mechanism casing with support frame: 10% fiberglass PC

Colour	White	Titanium
Rocker plate	ABS	Painted ABS
Plate	ABS + PC	-

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

■ 6.1.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day

ZigBee radio technology

Frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 6.1.4 Climate characteristics

Usage temperature: +5°C to +45°C

Storage temperature: 0°C to +45°C

■ 6.2 LEDVANCE SMART+ BULB

■ 6.2.1 Electrical characteristics

Dimmable

Voltage: 220 - 240 V~

Power: 60 W

Frequency: 50 Hz

Current: 55 mA

Service life: up to 20,000 hours

■ 6.2.2 Photometrics characteristics

Color: RGBW

Luminous flux: 806 lm

Color temperature: 2000 to 6500 K

■ 6.3 CONNECTION TERMINAL

■ 6.3.1 Electrical characteristics

Current: 24 A max.

Insulation voltage: 450 V~

7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (1 991 34/35) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com