


Mallia™ Senses

Emergency key switch

Cat. No(s): 2 810 49 MW - 2 810 49 MG
2 810 49 MB - 2 810 49 DS
2 810 49 CH - 2 810 49 DB
2 810 49 BA - 2 810 49 BB
2 810 49 BC



2 810 49 XX

1. USE

Security switch used for emergencies.
(Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)


2. RANGE

Designation	Cat. No.
EMERGENCY KEY SWITCH	2 810 49 XX

Colours

-Front: MW/MG/MB/DS/CH/DB/BA/BB/BC
-Rear: grey
2 81X XX MW Matt White
2 81X XX MG Matt Grey
2 81X XX MB Matt Black
2 81X XX DS Dark Silver
2 81X XX CH Champagne
2 81X XX DB Dark Bronze
2 81X XX BA Brushed Aluminium
2 81X XX BB Brushed Black
2 81X XX BC Brushed Champagne

3. DIMENSIONS (mm)



References	A	B	C	D
2 810 49 XX	86	86	41	34.3

4. CONNECTION

4.1 Terminal

Types of terminals: with screws
Terminal capacity: $2 \times 1 \text{ mm}^2$
 $2 \times 1.5 \text{ mm}^2$
Recommended stripping length: 12 mm
Recommended screwdriver size: <4 mm flat blade

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Plate: PC
Frame: Steel
Base: PC
Self-extinguishing:
+ 850°C / 30 s for insulating parts holding live parts in place
+ 650°C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Voltage: 250V~
Current: 1A

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C
Operating temperatures: -5°C to +50°C

5.4 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP20

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.
Do not use: acetone, tar remover, trichloroethylene.

7. CONFORMITY - APPROVALS

Compliant with installation and manufacturing standards.
See e-catalogue.