


1. USE

For recharging portable devices such as phones, smartphones, MP3 or MP4, loudspeakers, watches, game consoles, powerbanks.

2. RANGE

15 W USB charger	White	Magnesium	Champagne	Soft Alu
USB Type A+A charger	5 716 84	5 716 85	5 716 86	5 716 87

3. OVERALL DIMENSIONS (mm)



4. CONNECTION

Type of terminals: with screws Terminal capacity: 1 x 2.5 mm² - 2 x 1.5 mm² Stripping length: 6 mm Circuit Breaker: MAX. 16 A

Necessary safety precautions:

Switch OFF the power at the main circuit breaker. Make sure that the power is OFF besfore continuing with the installation.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04 Penetration by solid bodies/liquid: IP 40

■ 5.2 Material characteristics

Base: PC V-0 class Cover: painted PC V-0 class

Self-extinguishing:

 850°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of $+ 20^{\circ}$ and after 30 minutes of operation.

Nominal input voltage	100-240 V~			
Nominal input frequency	50/60 Hz			
Nominal input current	0.5 A			
Max. nominal output current	3.0 A			
Max. output power	15 W			
Nominal output voltage	5.0 V==			
Average efficiency in active mode	85 %			
Stand-by power consumption	< 0.1 W			
Consumption class without load and average level of efficiency: Level VI				
Protection class	ll - Low voltage			

Note: To optimize the charging time of your device, ensure turn it offduring the charging phase.

■ 5.4 Climate characteristics

Storage temperature: -20° C to $+70^{\circ}$ C Operating temperature: $+5^{\circ}$ C to $+40^{\circ}$ C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e.catalogue