


# Micromodule for 2-speed exhaust fan

Cat. No(s): 0 677 66



#### 1. USE


2-speed exhaust fan micromodule. To be installed inside an IP4X box.

Can be associated with one or more wireless controls for VMC.

#### 2. RANGE

Description	Cat. No
Micromodule for 2-speed VMC With LED indicator (configuration) and RESET button (hidden)	0 677 66
used to return to factory settings.	

# 3. DIMENSIONS (mm)




# 4. CONNECTION

Type of terminals: with screws

Terminals capacity: 1 x 2.5 mm<sup>2</sup> - 2 x 1.5 mm<sup>2</sup>

Stripping length: 7 mm Screwdriver: flat blade 3 mm

#### 5. FUNCTION



#### **6. TECHNICAL CHARACTERISTICS**

### ■ 6.1 Mechanical chacaracteristics

Protection against impacts: IK 04 Protection against solid/bodies and liquids: IP 20

#### ■ 6.2 Material characteristics

Mechanism casing: PC

Cover-plate: ABS White RAL 9003

Self-extinguising:

850°C/30 s for insulating parts holding live parts in place. 650°C/30 s for the other insulating components.

### ■ 6.3 Electrical characteristics

Frequency band: 2.4 to 2.44835 GHz Power level: < 100 mW

	Motor
240 Vac max.	1 x 500 VA
100 Vac max.	1 x 270 VA

Voltage: 100/240 V~ Frequency: 50/60 Hz

#### ■ 6.4 Climate characteristics

Storage temperature: 0°C to +45°C Usage temperature: +5°C to +45°C

# Référence: 0 677 66

# 7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

### 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 677 66) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: **www.legrandoc.com** 

Compliant with installation and manufacturing standards. See e.catalogue.