


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tel.: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88 www.legrand.com

# Niloé<sup>™</sup> sélection\_

**RJ11 sockets** 



## 1. USE

Telephone sockets: Fitted with a modular Jack connector with 1/4-turn terminals for fast connection. Option of tap-off connection. RJ11 (4 contacts)


Mechanisms to be equipped with plates.

Screws or claws fixing.

#### 2. RANGE

Designation	Aluminium	Antharcite	Smoked grey	Pearl
RJ11 socket	7 621 69	7 622 69	7 623 69	7 624 69

## 3. OVERALL DIMENSIONS (mm)



## 4. CONNECTION

Maximum number of connections and disconnections: 5 without replacing the wire.

Endurance: 750 operations (plugging in/unplugging).

## **5. TECHNICAL CHARACTERISTICS**

## 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 21 Protection against impact: IK 04

#### 5.2 Material characteristics

Material: Cover-plate: ABS

Mechanism casing: PC Support: PC grey RAL 7037 Claws: Steel

Halogen-free UV-resistant

Self-extinguishing: 650°C/30 s

## 5.3 Electrical characteristics

Breakdown voltage 1000 VDC Contact resistance 20 m  $\Omega$  Insulation resistance 500 m  $\Omega$  at 100 VDC

## 5.4 Climate characteristics

Storage temperature :  $-10^{\circ}$ C to  $+70^{\circ}$ C Usage temperature:  $-5^{\circ}$ C to  $+40^{\circ}$ C

## **6. MAINTENANCE**

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

#### **current** with a set before a sing other special cleaning produces.

#### 7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e. catalogue.