



Mallia™ US sockets


Cat. No(s): 2 811 05/06 2 831 05/06
2 833 05/06 2 835 05/06




2 811 05



2 811 06



2 831 05
2 833 05
2 835 05



2 831 06
2 833 06
2 835 06


1. USE

Single and Duplex 2P+E US sockets (for US standard).
(Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE

Designation	White	Silver	Pearl	Dark silver
Single US 2P+E socket 1G	2 811 05	2 831 05	2 833 05	2 835 05
Duplex US 2P+E Socket 1G	2 811 06	2 831 06	2 833 06	2 835 06

3. DIMENSIONS (mm)



References	A	B	C	D
2 811 05	86	86	28.6	18.8
2 811 06	86	86	29.2	19.2
2 831 06	81.5	84	28.6	18.8
2 831 06	81.5	84	29.2	19.2
2 833 05	81.5	84	28.6	18.8
2 833 06	81.5	84	29.2	19.2
2 835 05	81.5	84	28.6	18.8
2 835 06	81.5	84	29.2	19.2

4. CONNECTION

Types of terminals: with screws

Terminal capacity(L,N): 3 × 2.5 mm²
3 × 4 mm²
2 × 6 mm²

Terminal capacity(Earth): 3 × 2.5 mm²
1 × 4 mm²
1 × 6 mm²

Recommended stripping length: 12 mm

Recommended screwdriver size: 4 mm flat blade

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Plate: PC

Frame: PC

Support: PC

Base: PP

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Voltage: 127V~ Current: 15A

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C

Operating temperatures: -5°C to +50°C

5.4 Mechanical characteristics

Impact test: IK04

Protection against solids & liquids: IP41

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.

Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform with installation and manufacturing standards.

Refer to e-catalogue.