



Suno™ Lighting controls 16 AX Cat. No(s): 7 21X 04/14






1. USE

Lighting controls mechanism 16 AX - 250 V \sim . Flush-mounting or surface-mounting. Screw and/or claw fixing.


2. RANGE

| 16AX Switch with automatic terminal | White | lvory | Aluminum | Black |
|-------------------------------------|----------|----------|----------|----------|
| 1-WAY SWITCH | 7 211 04 | 7 212 04 | 7 213 04 | 7 214 04 |
| 1-WAY SWITCH ILLUMINATED | 7 211 14 | 7 212 14 | 7 213 14 | 7 214 14 |

3. DISMANTLING



4. DIMENSIONS (mm)



5. CONNECTION

Flexible or rigid cables compatible.

Type of terminals: Automatic terminal

Terminal capacity: 2 x 2.5mm2/terminal

Stripping length: 13mm

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20 Protection against impact: IK 04

■ 6.2 Material characteristics

Polygloss appearance

Colour molded:

- White RAL 9003 - Ivory RAL 1013

Matt colour painted:

- Aluminum RAL 9023 - Black RAL 9017

Material:

- Plate ABS
- Socket covers: Polycarbonate
- Halogen-free
- UV resistant

Self-extinguishing:

 850°C/30 s for insulating components holding live parts in place 650°C/30 s for other insulating components

■ 6.3 Electrical characteristics

Voltage: 250 V~ Current: 16 AX

Max. power for self-ballasted lamps: 100 W


Frequency: 50/60 Hz

■ 6.4 Climate characteristics

Usage temperature: - 5° C to + 35° C Storage temperature: - 10° C to + 70° C

■ 6.4 Support


Material of support: -Metal Angular adjusting:



■ 6.6 Fixing with claws

Number of turns to open the claws:

- 58 mm > 2,1 turns
- 65 mm > 2,75 turns



Updated: 30/05/2022

Performance of double teeth claws: extraction resistance:

7. MAINTENANCE

Surface cleaning with a cloth.

Do not use:

Acetone, tar remover, trichlorothylene.

Technical data sheet: F03655EN/00

Maintenance with the following products:

Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products.

Caution: Always test before using other special cleaning products.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. Refer to e-catalogue.

2/2