


Mosaic™ USB Type-A+A charger- 15 W

Cat. No(s): 0 776 60L/61L/62L




1. USE

For recharging portable devices such as phones, smartphones, MP3 or MP4, loudspeakers, watches, game consoles, powerbanks.
Exclusive mounting on tertiary supports.
For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings.
Not compatible with Batibox flush-mounting boxes.

2. RANGE

15 W USB charger	White	Alu	Black
USB Type-A+A charger 1 module	0 776 60L	0 776 61L	0 776 62L

3. DIMENSIONS (mm)



A	B	C	D
45	22.5	41	8.5

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 1 x 2.5 mm² - 2 x 1.5 mm²
Stripping length: 6 mm
Screwdriver: flat 3.5 mm
Circuit Breaker: MAX. 16 A

Necessary safety precautions:



**Switch OFF the power at the main circuit breaker.
Make sure that the power is OFF before continuing
with the installation.**

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04
Penetration by solid bodies and liquids: IP 40

■ 5.2 Material characteristics

Base: PC V-0 class
Cover: painted PC V-0 class

Self-extinguishing:
850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~
Nominal input frequency	50/60 Hz
Nominal input current	0.5 A
Max. nominal output current	3.0 A
Max. output power	15 W
Nominal output voltage	5.0 V~
Average efficiency in active mode	85 %
Stand-by power consumption	< 0.1 W
Consumption class without load and average level of efficiency:	Level VI
Protection class	II - Low voltage

*Note: European Standard (CE) No. 278/2009-6 April 2009, directive 2009/125/CE relating to ecodesign requirements for AC/DC power supplies.

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

■ 5.4 Climate characteristics

Storage temperature: -20°C to +70°C
Operating temperature: +5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e.catalogue