


British Standard plug 13 A




1. USE

2 P+E British Standard plug with integrated fuse for protection against overloads.

2. RANGE

Description	White/Grey
2 P+E male plug with integrated fuse. Side cable outlet.	6 500 13
To be plugged on 2P+E in wall socket outlet.	

3. DIMENSIONS (mm)



A	В	D
52	50	43

4. CONNECTION

Type of terminals: with screws Terminal capacity: 2.5 mm² MAX Cable: 3 x 1.5 mm² MAX

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against mechanical impact: IK 04 Protection against solid bodies and liquids: IP 20

5.2 Material characteristics

PP White RAL 9003/light Grey RAL 7047 L/N/E terminals: Brass Screws: Mild steel, plated

Halogen-free UV-resistant

Self extinguishing:

750°C/30 s for insulating components holding live parts in place. 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Voltage: 250 V~ Current: 13 A Power: 3250 W MAX. Frequency: 50/60 Hz

Integrated fuse:

13 A

5.4 Climate characteristics

Usage temperature: -5° C to $+35^{\circ}$ C Storage temperature: -20° C to $+70^{\circ}$ C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e. catalogue.