


Multi-standard multi-outlet extension cord switched with fuse With or without USB ports

Cat. No(s): 6 985 00/01/02/44/45/74/75



1. USE

Multi-outlet extensions: available with 4 and 5 socket outlets with shutters + 4 or 5 switches with indicator light, with 2 P+E BS plug equipped with a cord 3 or 5 m (H05VVF 3 G 1.25 mm²).

With overload fuse protection.


With 2 USB Type-A charging module (for Cat. Nos 6 985 00/01/02).

Can be fixed with screws onto a wall, piece of furniture, work surface (vertical and horizontal positioning adjustment).

2. RANGE

MULTI-OUTLET EXTENSIONS ADAPTED FOR MULTI-STANTARDS PLUGS	Cable length 3 m 3 G 1.25 mm ²		Cable length 5 m 3 G 1.25 mm ²
	White/Grey	Black	White/Grey
4 x 2P+E + 4 switches with indicator light + fuse + cable	6 985 44	-	6 985 74
5 x 2P+E + 5 switches with indicator light + fuse + cable	6 985 45	-	6 985 75
4 x 2P+E + 4 switches with indicator light + fuse + cable with 2 USB Type-A charging module - 2.4 A MAX.	6 985 00	6 985 02	6 985 01

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
6 985 00/01/02	80	340	32
6 985 45/75	75	341	32
6 985 44/74	80	270	30

Multi-standard multi-outlet extension cord switched with fuse With or without USB ports

Cat. No(s): 6 985 00/01/02/44/45/74/75

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Protection against mechanical impact: IK 04

Protection against solid bodies and liquids: IP 20

■ 4.2 Material characteristics

Switch: PP

End cap: PVC

Shutters: PA 6.6 + fiberglass

Matt white RAL 9003/Grey light RAL 7047

Matt black RAL 9004

Halogen-free

UV-resistant

Self extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

■ 4.3 Electrical characteristics

2 P+E socket outlets:

Voltage: 230 V~

Frequency: 50 Hz

Current: 13 A

Power: 3250 W MAX.

Integrated fuse:

Current: 13 A

USB:

2 USB Type-A port

2.4 A MAX.

5.0 V=

12.0 W MAX.

Average active efficiency: 81 %

Electricity consumption when not charging: 0.07 W

■ 4.4 Climate characteristics

Usage temperature: - 5°C to + 35°C

Storage temperature: - 20°C to + 70°C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Caution: Always test before using other special cleaning products.

6. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e. catalogue.