



Eloe™ Senses

Multistandard switched socket


Cat. No(s): 6 180 65/67/69



6 180 65



6 180 67



6 180 69


1. USE

One and two gang switched multistandard socket.
 (Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE

Designation	White
1 GANG 13A SWITCHED MULTISTANDARD + EUR-US SOCKET SWITCHED	6 180 65
1 GANG MULTISTANDARD SINGLE POLE SWITCHED SOCKET	6 180 67
2 GANG MULTISTANDARD SINGLE POLE SWITCHED SOCKET	6 180 69

3. DIMENSIONS (mm)



References	A	B	C	D
6 180 65	86	86	38.5	26.6
6 180 67	86	86	32.9	21.1
6 180 69	86	146	32.9	21.1

Recommended box depth \geq 35 mm

4. CONNECTION

Types of terminals: with screws
 Terminal capacity: 3 \times 1 mm²
 3 \times 1.5 mm²
 2 \times 2.5 mm²
 1 \times 4 mm²

Recommended stripping length: 12 mm
 Recommended screwdriver size: <4 mm flat blade

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Rocker: PC
 Plate: PC
 Frame: PC
 Base: PC
 Self-extinguishing:
 + 850° C / 30 s for insulating parts holding live parts in place
 + 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Multistandard Socket:
 Voltage: 127V~ Current: 15A
 Voltage: 250V~ Current: 2.5/5/6/10/13/16A
 Frequency: 50/60Hz

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C
 Operating temperatures: -5°C to +35°C

5.4 Mechanical characteristics

Impact test: IK04
 Protection against solids & liquids: IP20

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.
 Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform with installation and manufacturing standards.
 Refer to e-catalogue.