


Shaver Socket

Cat. No(s): 7 482 41
7 484 41
7 486 41



7 482 41
7 484 41
7 486 41

5. TECHNICAL CHARACTERISTICS

5.1 Material characteristics

Plate: PC
Frame: PC
Base: PC
Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

Transformer: primary and secondary 240 V - 115/240 V
Frequency: 50/60 Hz
Power: 20VA Max.

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C
Operating temperatures: -5°C to +35°C

5.4 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP24

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.
Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform to BS EN 61558-2-5.


Device for the supply of electric shavers requiring either a 240V or 115V supply and having a power consumption not exceeding 20VA. Accepts the following types of plug: BS, Euro, US, Australian and Chinese. (Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE

Shaver Socket

7 482 41	● Satin Brass
7 484 41	● Brushed stainless steel
7 486 41	● Polished stainless steel

3. DIMENSIONS (mm)



References	A	B	C	D
7 482 41				
7 484 41	86	146	50.8	40.6
7 486 41				

4. CONNECTION

Types of terminals: auto terminal
Terminal capacity: 2 X 1.5 mm²
2 X 2.5 mm²
Recommended stripping length: 13 mm