



## Arteor™ with Netatmo - British Standard Connected starter pack

Cat. Nos: 5 746 01/02/03/04



Gateway



General control

### 1. USE

This pack enables you to create a connected installation in your home.  
 It can be used to control lighting, roller shutters and electrical equipment plugged into connected products

- using your smartphone and the Home + Control app
- using voice assistants
- from the general control at the entrance to your home

**Comprises:**

• **A gateway (Zigbee relay/WiFi)**

Installation in 1-gang box 35 mm deep (minimum).  
 Claw and/or screw fixing.


• **A wireless general control**, used to control leaving home/coming home scenes involving lights, roller shutters and connected sockets.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Fits on a piece of furniture (movable).


### 2. RANGE

Description	White	Magnesium	Soft Alu	Champagne
<b>Gateway:</b> To be equipped with support frame and plate  <b>Additional wireless general control:</b> Supplied with secable support frame, rocker plate and a battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied).	5 746 01	5 746 02	5 746 03	5 746 04

### 3. DIMENSIONS (mm)




Gateway	A	B	C	D
	45	45	46	12.5



Wireless General Control	A	B	B'	C
	82	116.5	82	12

#### 4. OPERATION



**!** The starter pack is pre-paired at the factory. Never perform a factory RESET on the gateway module and the wireless general control at the same time, as this may render them unusable.

#### 5. CONNECTION

##### Gateway

Terminal type: with screws  
Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
Stripping length: 9 mm

#### 6. TECHNICAL CHARACTERISTICS

##### ■ 6.1 Mechanical characteristics

###### Gateway:

Protection against impacts: IK 04  
Protection against solid bodies and/or liquids: IP 40 mounted product

###### General control:

Protection against impacts: IK 02  
Protection against solid bodies/liquids: IP 20

##### ■ 6.2 Material characteristics of gateway

Cover plate: PC  
Mechanism casing: PC  
Halogen-free  
UV-resistant

Self-extinguishing:  
850°C/30 s for insulating components holding live parts in place.  
650°C/ 30 s for other insulating components.

#### 6. TECHNICAL CHARACTERISTICS (continued)

##### ■ 6.3 Material characteristics of general control

Mechanism casing with grid: Fibreglass-reinforced (20%) PC  
Halogen-free  
UV resistant  
Self-extinguishing: 650°C/30 s

##### ■ 6.4 Electrical characteristics

Voltage: 110/230 V~  
Standby consumption: 10 mA

##### WiFi technology

Frequency: 2.4 GHz to 2.4835 GHz  
Power level: < 100 mW

Range: 200 m of unobstructed space  
10 m recommended between products indoors

##### General control

Powered by a CR2032 - 3 V lithium battery (supplied)  
Battery life: 8 years for 10 activations a day

##### ■ 6.5 Climate characteristics

Storage temperature: 0°C to + 45°C  
Usage temperature: +5°C to + 35°C

#### 7. CARE

Clean the surface with a cloth.  
Do not use acetone, tar-removing cleaning agents or trichloroethylene.  
Resistant to the following products:  
Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.



Take care to recycle the battery appropriately.

#### 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 746 01/02/03/04) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: [www.legrandoc.com](http://www.legrandoc.com)