



Arteor™ with Netatmo - British Standard Connected switches with neutral


Cat. No(s): 5 746 05/06/07/08/09/10/11/12/13/14/15/16



5 746 05



5 746 09



5 746 13


1. USE

For local or remote control of lighting devices and other controls.
Can be combined with one or more wireless lighting controls.
Can be installed in place of an existing switch in a flush-mounting box 25 mm deep (minimum).

2. RANGE

Description	White	Magnesium	Soft Alu	Champagne
Product for use in conjunction with the starter pack. With LED indicator (configuration) and RESET button (hidden) used to return to factory settings. Locator and indicator modes can be activated from the Home + Control App.	5 746 05 1-gang	5 746 06 1-gang	5 746 07 1-gang	5 746 08 1-gang
	5 746 09 2-gang	5 746 10 2-gang	5 746 11 2-gang	5 746 12 2-gang
	5 746 13 3-gang	5 746 14 3-gang	5 746 15 3-gang	5 746 16 3-gang

3. DIMENSIONS (mm)





A	B	C	D
81.5	81.5	31	10.5

4. CONNECTION

Terminal type : with screws
Terminal capacity: 2 x 1.5 mm² - 2 x 2.5 mm² - 1 x 4 mm²
Stripping length: 8 mm



5. OPERATION

1-gang: 5 746 05/06/07/08





5. OPERATION (continued)

2-gang: 5 746 09/10/11/12



3-gang: 5 746 13/14/15/16



6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against impacts: IK 04
Protection against solid bodies and liquids: IP 20

■ 6.2 Material characteristics

Rocker plate: ABS White RAL 9003
ABS Magnesium painted
ABS Soft Alu painted
ABS Champagne painted

Mechanism casing: PC

Halogen-free
UV-resistant

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

■ 6.3 Electrical characteristics

Voltage: 110/240 V~
Frequency: 50/60 Hz
Standby consumption: 0.1 mA

Zigbee technology

Frequency: 2.4 GHz to 2.4835 GHz
Power level: < 100 mW

Range: 200 m of unobstructed space
10 m between products indoors

■ 6.4 Climate characteristics

Storage temperature: 0°C to + 45°C
Usage temperature: +5°C to + 35°C

7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 746 05/06/07/08/09/10/11/12/13/14/15/16) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com