



Arteor™ with Netatmo - British Standard Connected ON/OFF wireless controls for lighting and socket outlets


Cat. Nos: 5 746 63/64/65/66/67/68/69/70/71/72/73/74



5 746 63/64/65/66



5 746 67/68/69/70



5 746 71/72/73/74

1. USE

Wireless controls for ON/OFF/dimming light functions or connected socket outlets.

This product controls "with Netatmo" micromodule products, connected socket outlets and connected switches.

Can be used as a two-way switch or to control a lighting group.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Fits on furniture (movable).

1-gang can be combined with 20 wired products.


2-gang can be combined with 2 x 20 wired products.

3-gang can be combined with 3 x 20 wired products.

2. RANGE

Description	White	Magnesium	Soft Alu	Champagne
Wireless lighting and socket outlets controls, for an ON/OFF, dimming, centralisation function. Supplied with secable support frame, rocker plate and a battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied).	5 746 63 1-gang	5 746 64 1-gang	5 746 65 1-gang	5 746 66 1-gang
	5 746 67 2-gang	5 746 68 2-gang	5 746 69 2-gang	5 746 70 2-gang
	5 746 71 3-gang	5 746 72 3-gang	5 746 73 3-gang	5 746 74 3-gang


3. DIMENSIONS (mm)



A	B	B'	C
82	116.5	82	12



4. OPERATION

1-gang: 5 746 63/64/65/66





4. OPERATION (continued)

2-gang: 5 746 67/68/69/70



3-gang: 5 746 71/72/73/74



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02
Protection against solid bodies and/or liquids: IP 20

■ 5.2 Material characteristics

Rocker plate: ABS
Mechanism casing with grid: Fibreglass-reinforced (20%) PC
Halogen-free
UV-resistant
Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)
Battery life: 8 years for 10 activations a day

ZigBee radio technology

frequency: 2.4 GHz to 2.4835 GHz
Power level: < 100 mW

■ 5.4 Climate characteristics

Storage temperature: 0° C to + 45° C
Usage temperature: +5° C to + 35° C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:
Hexane), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 746 63/64/65/66/67/68/69/70/71/72/73/74) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com